

APC Back-UPS Pro, 1000VA/600W, Tower, 120V, 10x NEMA 5-15R outlets, Sine Wave, AVR, USB Type A + C ports, LCD, User Replaceable Battery

BR1000MS

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time	Usually in Stock
Main	
Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	600 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R 4 NEMA 5-15R surge
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery
Range of Product	Back-UPS Pro

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	1
Battery Voltage	24 V
Battery Capacity	7.0 Ah
Battery Charge Power (Watts)	8 W rated
Battery life	35 year(s)
Replacement battery	APCRBC160 ☐
Extendable Run Time	0

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

General

Provided equipment	Coaxial cable User Manual USB cable
product web sub-family	Gaming performance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

color	Black
Height	10.24 in (26 cm)
Width	3.94 in (10 cm)
Depth	14.49 in (36.8 cm)
Net Weight	22.5 lb(US) (10.2 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	60 Hz +/- 3 Hz
Plug standard	NEMA 5-15P
Efficiency at full load	88147 V
Maximum Input Current per Phase	12 A
Switching current capacity	15 A

Output

Max Configurable Power (Watts)	600 W
Output Frequency (sync to mains)	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Wave type	Sine wave
Maximum configurable power in VA	1000 VA
Transfer Time	8ms typical : 10 ms maximum

Conformance

Product Certifications	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Equipment protection policy	Lifetime · \$250000

Environmental

Ambient air temperature for	32104 °F (040 °C)	
operation		

Relative Humidity	095 % non-condensing	
Operating altitude	03000 ft	
Ambient Air Temperature for Storage	5104 °F (-1540 °C)	
Storage Relative Humidity	095 % non-condensing	
Storage altitude	05000 ft (0.00000000001524.0000000000 m)	
Acoustic level	45 dBA	

Communications & Management

control panel	Multi-function LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	1080 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	00731304335382
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	14.12 in (35.87 cm)	
Package 1 Width	18.98 in (48.2 cm)	
Package 1 Length	8.78 in (22.3 cm)	
Package 1 Weight	26.01 lb(US) (11.8 kg)	
SCC14	10731304335389	

Contractual warranty

Warranty 3 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

EU RoHS Directive	Compliant with Exemptions	
REACh Regulation	REACh Declaration	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
☼ Energy efficiency		
Optimized Energy Efficiency	Energy efficient product	
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)	

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes