

Product data sheet

Specifications



APC Smart-UPS On-Line, 3kVA, Rack/Tower, 120V, 8x 5-20R+1x L5-30R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit [TAA]

SRT3000XLAUS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V AC 1 phase
Input Connection Type	NEMA L5-30P
Input Frequency	40 - 70 Hz auto-sensing
Output voltage	120 V AC 1 phase
Rated power in W	2700 W
rated power in VA	3000 VA
output connection type	8 NEMA 5-20R 1 NEMA L5-30R
Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Topology	On-Line
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Lead-acid internal included
Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Audible and visible alarms : prioritized by severity
UPS connectivity	Serial port USB port
Surge energy rating	340 J
Cable length	7.9 ft (2.4 m)
Number of cables	1
color	Black
Height	17.008 in (432 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	3.3 in (85 mm)
Depth	25 in (635 mm)
Net Weight	69.005 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical
Mounting mode	Tower
Provided equipment	CD with software Documentation CD Installation guide Removable support feet USB cable Warranty card
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	TAA compliance
Redundant	No
Range of Product	Smart-UPS On-Line
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	TAA compliance ENERGY STAR V2.0 (USA)
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dBA
Online Thermal Dissipation	805 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Extendable Run Time	1
Included Battery Modules	1
Typical recharge time	3 h

RBC Quantity	1
Battery Life	3...5 year(s)
Replacement battery	APCRBC152 
Battery Charge Power (Watts)	151 W rated

Ordering and shipping details

GTIN	731304340478
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.7 in (24.6 cm)
Package 1 Width	34.3 in (87.1 cm)
Package 1 Length	23.6 in (59.9 cm)
Package weight(Lbs)	81.00 lb(US) (36.74 kg)

Compliance

Compliance	TAA Compliant
------------	---------------

Contractual warranty

Warranty (in months)	24 Battery 36 UPS
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	7 985 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	461 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	5 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	7 514 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold



Energy efficiency



ENERGY STAR®

ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	65
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

