

Product data sheet

Specifications



APC Temperature & Humidity Sensor



AP9335TH

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Presentation	This Temperature & Humidity Sensor is a Universal sensor that monitors temperature and humidity in your Data Center or Network Closet. IT has an RJ-45 connector. The cord length is 3.9m.
Lead time	Usually in Stock

Main

Product or Component Type	Temperature and humidity sensor
Range of Product	Netbotz
Number of rack unit	0U
Provided Equipment	Humidity sensor Installation guide Temperature Sensor

Physical

Color	Black
Height	0.2 in (0.6 cm)
Width	0.2 in (0.5 cm)
Depth	0.2 in (0.5 cm)
Net Weight	0.40 lb(US) (0.18 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Environmental

Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0...15240 m)
Storage Relative Humidity	0...95 %

Ordering and shipping details

Category	09305 - INDUSTRIAL UPS
GTIN	731304234005
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	IN
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	0.4 in (1 cm)
------------------	---------------

Package 1 Width	10.0 in (25.4 cm)
-----------------	-------------------

Package 1 Length	6.0 in (15.2 cm)
------------------	------------------

Package weight(Lbs)	0.615 lb(US) (0.279 kg)
---------------------	-------------------------

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	0.6 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.6 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer




Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.