

Product data sheet

Specifications



APC Smart-UPS On-Line, 10kVA/10kW, Rack/Tower, 208V, 4x L6-20R+2x L6-30R NEMA outlets, Network Card+SmartSlot, Extended runtime, W/O rail kit, TAA

SRT10KXLTUS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Kw Rating	10000 W
Rated power in VA	10000 VA
Output connection type	4 NEMA L6-20R 2 NEMA L6-30R
Output connector type	Hard Wire 3-wire (2PH + G) 1
Provided equipment	CD with software Documentation CD Installation guide Temperature Probe USB cable Warranty card Web/SNMP Management Card
Range of Product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-Acid battery
Extendable Run Time	1
Included Battery Modules	0
Typical recharge time	1.5 h
RBC Quantity	2
Battery life	3...5 year(s)
Replacement battery	APCRBC140
Battery Charge Power (Watts)	1191 W rated

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	TAA compliance
Redundant	No
Topology	Double Conversion Online

Physical

color	Black
Height	17.01 in (43.2 cm)
Width	10.35 in (26.3 cm)
Depth	28.15 in (71.5 cm)
Net Weight	245.99 lb(US) (111.58 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	100...275 V adjustable (half load)
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Input Frequency	40 - 70 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	10000 VA
Max Configurable Power (Watts)	10000 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A NOM TAA compliance UL 1778
------------------------	---

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	2490 Btu/h
Operating altitude	0...10000 ft

Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.000000000...15240.000000000 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency Power Off (EPO)	Yes
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rating	480 J
---------------------	-------

Ordering and shipping details

GTIN	731304340454
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.15 in (46.1 cm)
Package 1 Width	39.37 in (100 cm)
Package 1 Length	23.62 in (60 cm)
Package 1 Weight	279.00 lb(US) (126.55 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **22904**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

REACH Regulation [REACH Declaration](#)

Energy efficiency

Optimized Energy Efficiency **Energy efficient product**

ENERGY STAR® **ENERGY STAR UPS V2.0 (USA)**

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Removable battery **User replaceable**

Take-back **Yes**