

Product data sheet

Specifications



APC NetShelter Basic Rack PDU,
1U, 1 phase, 3.7kW 230V 16A or
3.3kW 208V 16A, 12 C13 outlets,
C20 cord

AP9565

Overview

Presentation Reliable rack power distribution designed to increase manageability and efficiency in the data center. The output and input connections are (12)C13. Real-time remote monitoring of connected loads. User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Basic

Cord length 8.17 ft (2.49 m)

Number of cables 1

Provided Equipment Installation guide
Rack Mounting brackets

Complementary

Input Voltage 200 V
208 V
230 V

Height 1.7 in (44 mm)

Width 17.6 in (447 mm)

Output Voltage 208 V
230 V

Depth 2.2 in (57 mm)

Net Weight 4.52 lb(US) (2.05 kg)

Mounting Location Front
Rear

Mounting preference No preference

Input Plug Type IEC 60320 C20

Mounting Mode Rack-mounted

Rack units 1U

Mounting position Horizontal

Input current limits 16 A

Load Capacity 3680 VA

Input Frequency 50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	12 IEC 60320 C13
--------------------------	------------------

Environment

Product Certifications	cUL Listed CE Queensland Australia UL Listed VDE
------------------------	--

Standards	UL 60950
-----------	----------

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
-------------------------------------	----------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0...15240 m)
------------------	----------------------------

Ordering and shipping details

GTIN	731304213055
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	2.8 in (7 cm)
------------------	---------------

Package 1 Width	18.3 in (46.4 cm)
-----------------	-------------------

Package 1 Length	9.02 in (22.9 cm)
------------------	-------------------

Package weight(Lbs)	8.007 lb(US) (3.632 kg)
---------------------	-------------------------

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 398 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.3 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 385 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.2 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



