

Product data sheet

Specifications



APC NetShelter Basic Rack PDU, 0U, 16A, 208/230V, 15 C13 outlets



AP9572

Overview

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Basic

Cord length 7.9 ft (2.4 m)

Number of cables 1

Provided Equipment Rack Mounting brackets
Toolless Mounting Kit
User Manual

Complementary

Input Voltage 200 V
208 V
230 V

Height 24.4 in (620 mm)

Width 1.7 in (44 mm)

Output Voltage 200 V
208 V
230 V

Depth 1.7 in (44 mm)

Net Weight 4.4 lb(US) (2 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type IEC 60320 C20

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Max line current 16 A

Input current limits 16 A

Load Capacity 3680 VA

Input Frequency 50/60 Hz

Outlet type and quantity 15 IEC 60320 C13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed CE Queensland Australia UL Listed VDE
Standards	UL 60950
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304226369
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	25.1 in (63.8 cm)
Package 1 Width	6.6 in (16.8 cm)
Package 1 Length	5.7 in (14.6 cm)
Package weight(Lbs)	6.005 lb(US) (2.724 kg)

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	2 395 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.2 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 385 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.2 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

Use Longer

Lifetime extension

Repair	No
--------	----

Use Again

Repack and remanufacture

Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative





