# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Rack Mount, Security and Environmental Appliance, NetBotz, 750



NBRK0750

### **Overview**

Presentation	The NetBotz Rack Monitor 750 provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes, from single-rack edge networks to large data centers.
Lead time	Usually in Stock

### Main

IVIAIII	
Product or Component Type	Industrial rack PC
Range of Product	Netbotz
Number of rack unit	1U
Communication Port Protocol	A-Link DHCP HTTPS IPv4 SNMP v1 SNMP v3 SSH v2 TCP/IP
Provided Equipment	Rack Mounting brackets Temperature/Humidity Sensor USB cable
Product Compatibility	Rack Sensor Pod 150 Room Sensor Pod 155

### **General**

Camera Frame Rate	Up to 30fps
Display Resolution	Up to 1280x1024
APC Universal Sensors Supported	0-5V Door contact Dry Contact Humidity Smoke Fluid Spot Leak Temperature Vibration
Number of Universal Sensor Ports	6
Number of Sensor Pods Supported	12
Number of Universal Sensors Supported	78
Number of Cameras Supported	4

### **Physical**

· <b>y</b> =	
Color	Black

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Height	1.69 in (4.3 cm)	
Width	17.01 in (43.2 cm)	
Depth	7.01 in (17.8 cm)	
Net Weight	5.40 lb(US) (2.45 kg)	
Mounting Location	Front Rear	
Mounting preference	No preference	
Mounting Mode	Rack-mounted	
Mounting position	Horizontal	

### Conformance

Standards	CSA C22.2 No. 60950-1-03	
	FCC Part 15 class A ICES-003	
	UL 60950-1	
Product Certifications	2014/30/EU AS/NZS 3548 (C-Tick) Class A CE	
	EMC Directive 2004/108/EC VCCI Class A	

## **Environmental**

Ambient air temperature for operation	32104 °F (040 °C)
Operating altitude	010000 ft
Relative Humidity	095 %
Ambient Air Temperature for Storage	5149 °F (-1565 °C)
Storage altitude	050000 ft (0.000000000015240.0000000000 m)
Storage Relative Humidity	095 %

# **Communications & Management**

Communication Network Type RJ-45 10/100/1000 Base-T

# Ordering and shipping details

GTIN 731304344407

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	4.53 in (11.500 cm)	
Package 1 Width	12.40 in (31.500 cm)	
Package 1 Length	21.06 in (53.500 cm)	
Package 1 Weight	9.178 lb(US) (4.163 kg)	
Unit Type of Package 2	S04	
Number of Units in Package 2	2	
Package 2 Height	11.81 in (30 cm)	
Package 2 Width	15.75 in (40 cm)	

Package 2 Length	23.62 in (60 cm)	
Package 2 Weight	19.789 lb(US) (8.976 kg)	
Unit Type of Package 3	P12	
Number of Units in Package 3	8	
Package 3 Height	17.72 in (45.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	105.610 lb(US) (47.904 kg)	

# **Contractual warranty**

Warranty 2 years



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### **Use Better**

EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No