

# Product data sheet

Specifications



## APC NetShelter Power Cord, Locking, IEC C19 to C20, 3.0m



AP8760

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Overview

**Presentation** Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

**Lead time** Usually in Stock

### Main

**Product or Component Type** Power cord

**Input Connection Type** IEC 60320 C20

**Cable length** 9.8 ft (3 m)

**Number of cables** 1

### Physical

**Color** Black

**Height** 9.06 in (230 mm)

**Width** 9.06 in (230 mm)

**Depth** 1.8 in (45 mm)

**Net Weight** 1.12 lb(US) (0.51 kg)

**Mounting preference** No preference

**Mounting Mode** Not rack-mountable

### Input

**Max line current** 16 A

### Output

**Maximum Total Current Draw per Phase** 16 A

**Number of power socket outlets** 1 IEC 60320 C19

**Cord Length** 10 ft (3.05 m)

### Conformance

**Product Certifications** CCC  
CSA  
PSE  
UL Listed  
VDE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0...15240 m)

## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304288145
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	9.06 in (23 cm)
Package 1 Length	1.8 in (4.5 cm)
Package weight(Lbs)	1.12 lb(US) (0.51 kg)

## Contractual warranty

Warranty (in months)	24
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	59 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	2 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	56 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.9 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
California proposition 65	<b>WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a></b>
Halogen content performance	Product contains halogen above thresholds

### Use Longer

#### Lifetime extension

Repair	No
--------	----

### Use Again

#### Repack and remanufacture

Recyclability potential, in %	30
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.