

Product data sheet

Specifications



APC Smart-UPS, Line Interactive, 750VA, Rackmount 2U, 230V, 4x IEC C13 outlets, SmartConnect Port+SmartSlot, AVR, LCD

SMT750RMI2UC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Kw Rating	500 W
Rated power in VA	750 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C14
output connection type	4 IEC 320 C13 2 IEC Jumpers
Number of rack unit	2U
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	Documentation CD Installation guide Rack Mounting support rails USB cable
Range of Product	Smart-UPS


Complementary

Communication port type	SmartConnect Ethernet port SmartSlot
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Additional information	Configurable for 220 : 230 or 240 nominal output voltage

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	4...6 year(s)
Replacement battery	APCRBC123 
Battery Charge Power (Watts)	56 W rated

General

Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

color	Black
Height	3.39 in (8.6 cm)
Width	17.01 in (43.2 cm)
Depth	16.10 in (40.9 cm)
Net Weight	36.6 lb(US) (16.6 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	151...302 V adjustable 160...286 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	750 VA
Max Configurable Power (Watts)	500 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE EAC RCM TÜV VDE UK PSTI
-------------------------------	---

Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
------------------	--

Environmental

Acoustic level	42 dBA
Online Thermal Dissipation	46 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Optional
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	459 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304340324
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.00 in (58.420 cm)
Package 1 Width	21.50 in (54.610 cm)
Package 1 Length	9.50 in (24.130 cm)
Package 1 Weight	46.701 lb(US) (21.183 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
-----------------	---

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) 821

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

[EU RoHS Directive](#) Compliant with Exemptions

REACH Regulation [REACH Declaration](#)

Energy efficiency

Optimized Energy Efficiency Energy efficient product

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Removable battery User replaceable

Take-back Yes