

Product data sheet

Specifications



NetShelter SX 12U/18U Roof 900mm Deep Black

AR7260

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Enclosure
Provided equipment	Grommets Installation guide Mounting Hardware

Physical

Color	Black
Height	32.7 in (830 mm)
Width	26.4 in (670 mm)
Depth	4.7 in (120 mm)
Net Weight	16.5 lb(US) (7.5 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Marking	16 gauge roof

Ordering and shipping details

GTIN	731304348047
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	4.7 in (12 cm)
Package 1 Width	26.4 in (67 cm)
Package 1 Length	32.7 in (83 cm)
Package weight(Lbs)	16.5 lb(US) (7.5 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	26 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	25 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.6 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.6 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Take-back	No