

Product data sheet

Specifications



APC Netshelter SX, Server Rack Enclosure, 18U, Black, 925H x 600W x 1070D mm [TAA]

AR3106

Overview

Presentation An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 18U

Provided equipment Casters
Doors
Key(s)
Leveling feet
Roof
Side Panels

Physical

Height 36.4 in (925 mm)

Width 23.6 in (600 mm)

Depth 42.1 in (1070 mm)

Net Weight 159.00 lb(US) (72.12 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 36.3 in (920.8 mm)

Minimum Mounting Depth 7.5 in (191 mm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 900 lb(US) (408.2 kg) dynamic
900 lb(US) (408.2 kg) static

Conformance

Standards UL 2416
UL 60950-1
EIA-310E

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

GTIN 731304347699

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	41.7 in (106 cm)
Package 1 Width	45.7 in (116 cm)
Package 1 Length	29.5 in (75 cm)
Package weight(Lbs)	205.03 lb(US) (93 kg)

Compliance

Compliance TAA Compliant
BAA Compliant via COTS

Contractual warranty

Warranty (in months) 60



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	326 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	312 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	8 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

