

HP ScanJet Pro N4000 snw1 Sheet-feed Scanner (6FW08A)



Get fast, two-sided scans in a single pass—recommended for 4000 pages per day.

Fast, affordable, and designed to handle everything from simple color jobs to complex workflows. Quickly and reliably digitize larger projects with scan speeds up to 40 ppm/80 ipm and a 50-page ADF. [1] Recommended for 4,000 pages per day.



Fast scanning. Superb results. Every page.

Produce scans at up to 40 ppm/80 ipm[1] with two-sided scanning that captures both sides at once.

Optimize workflows with one-touch scanning

Streamline routine work with one-touch scanning—create one-button, custom settings for recurring scan jobs.

Capture business documents like a pro

Tackle tasks quickly and easily - with the simple 2.8" color touchscreen

Featuring

Support Ethernet, WiFi and WiFi direct

One-pass duplex scanning

4000-page duty cycle

HP Scan software

50-page ADF

Compact size



Specifications

Scanner advanced features	Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Advanced multi-feed detection, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Delete blank page, Merge pages, Hole fill, PDF permissions, Document separation (Blank page, Barcode, Zonal barcode, Zonal OCR)
Connectivity, standard	Ethernet 10/100 Base-T, USB 3.0, WiFi 802.11 b/g/n, WiFi Direct
Wireless capability	Yes, WiFi 802.11 b/g/n, WiFi Direct
Network protocols, supported	ARP;ICMP; IGMP;UDP;TCP;DHCP;APIPA;DNS;mDNS;LLMNR;WSD;WS-Scan;SNTP;SMB;SNMP;FTP;SFTP;SMTP;HTTP Server Part;HTTPS
Software included	Windows: HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan, HP Scanner Tools Utility, OpenText ISIS
Compatible Operating Systems	Microsoft® Windows® (10, 8.1, 7, XP: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); MacOS (Catalina 10.15, Mojave 10.14, High Sierra 10.13); Linux (Ubuntu, Fedora, Debian, RHEL, Linux Mint, Open Suse, Manjaro); Citrix ready
Sustainable impact specifications	RoHS-compliant
Energy star certified	Yes
Ecolabels	CECP; ENERGY STAR® 3.0 certified; EPEAT® Silver
Digital sending standard features	Scan to PC, Scan to USB Drive, Scan to Email, Scan to Network Folder, Scan to SharePoint, Scan to Shortcut, Scan to Cloud
Scan file format	For text & images: PDF, PDF/A, Encrypted PDF, JPEG, PNG, BMP, TIFF, Word, Excel, PowerPoint, Text (.txt), Rich Text (.rtf) and Searchable PDF
Scan input modes	7.1 cm (2.8 inch) Color touch screen on front-panel for HP scan in Win OS, HP Easy Scan/ICA in Mac OS and third parties applications via TWAIN, ISIS and WIA
Scan technology	CMOS CIS (Contact Image Sensor)
Scanner type	Sheetfed
Display	Resistive, RGB color and 2.8 "touch panel with a resolution of 140 dpi (240 x 320 dots).
Minimum dimensions (W x D x H)	300 x 172 x 154 mm
Minimum dimensions (W x D x H)	11.8 x 6.8 x 6.1 in
Weight	2.8 kg
Weight	6.2 lb
Power consumption	5.9 Watts (ready), 24 Watts (scanning), 1.8 Watts (sleep), 0.1 Watts (auto-off), 0.1 Watts (off) ^[1] (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.)
Power supply type	External power adapter
What's in the box	Power cord; Power Adapter; USB Cable; Scanner Engine; Flyers; Install Guide
Manufacturer Warranty	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to hp.com/support to learn about HP world-class service and support options in your region.

Top Recommended Displays, Accessories and Services

HP ScanJet Maintenance Kits

HP ScanJet 2000s2/3000s4/4000snw1 Roller Replacement Kit	7QH79A
--	--------

Messaging Footnotes

[1] Scan speed measured at 300 dpi (black-and-white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

Technical Specifications Footnotes

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

