

# Product data sheet

Specifications



## APC NetShelter Switched Rack PDU, 9K series, 0U, 8.6kW, 208V, 21 C13 and C15, 3 C19 and C21 outlets

APDU9965

### Overview

Lead time Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	5.97 ft (1.82 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

### Complementary

Input Voltage	208 V 3 phase
Height	72.008 in (1829 mm)
Width	2.2 in (56 mm)
Output Voltage	208 V
Depth	2.008 in (51 mm)
Net Weight	18.03 lb(US) (8.18 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L21-30P
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	8600 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Outlet type and quantity</b>	21C13/C15 3C19/C21
<b>Communication Network Type</b>	10/100/1000BASE-T

## Environment

<b>Product Certifications</b>	cULus FCC part 15 class A
<b>Standards</b>	ICES-003
<b>Ambient Air Temperature for Operation</b>	23...140 °F (-5...60 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0...15240 m)

## Ordering and shipping details

<b>GTIN</b>	731304356325
-------------	--------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	80.3 in (204 cm)
<b>Package 1 Width</b>	4.9 in (12.4 cm)
<b>Package 1 Length</b>	6.5 in (16.5 cm)
<b>Package weight(Lbs)</b>	22.75 lb(US) (10.32 kg)

## Contractual warranty

<b>Warranty (in months)</b>	36
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	2 644 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	57 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 580 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Recyclability potential, in %	71
Circularity Profile	<a href="#">End of Life Information</a>
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

