

Product data sheet

Specifications



APC NetShelter Power Cord Kit (6 ea), Locking, C19 to C20, 1.2m

AP8714S

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

| | |
|----------------------------------|------------------|
| Product or Component Type | Power cord |
| Input Connection Type | IEC 60320 C20 |
| Cable length | 3.97 ft (1.21 m) |
| Number of cables | 6 |

Physical

| | |
|----------------------------|-----------------------|
| Color | Black |
| Height | 11.8 in (300 mm) |
| Width | 2.8 in (70 mm) |
| Depth | 2.8 in (70 mm) |
| Net Weight | 3.62 lb(US) (1.64 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |

Input

| | |
|-----------------------------|------|
| Max line current | 16 A |
| Input current limits | 16 A |

Output

| | |
|---|-----------------|
| Maximum Total Current Draw per Phase | 16 A |
| Number of power socket outlets | 1 IEC 60320 C19 |
| Cord Length | 4 ft (1.2 m) |

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------------------|---------------------------------------|
| Product Certifications | CCC CSA PSE UL Listed VDE |
|-------------------------------|---------------------------------------|

Environmental

| | |
|--|----------------------------|
| Ambient Air Temperature for Operation | 32...167 °F (0...75 °C) |
| Relative Humidity | 20...80 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | -13...167 °F (-25...75 °C) |
| Storage Relative Humidity | 20...80 % |
| Storage altitude | 0...50000 ft (0...15240 m) |

Ordering and shipping details

| | |
|--------------------------|-----------------------------|
| Category | 11309 - APC RESALE PRODUCTS |
| GTIN | 731304279709 |
| Returnability | No |
| Country of origin | CN |

Packing Units

| | |
|-------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 11.8 in (30 cm) |
| Package 1 Width | 2.8 in (7 cm) |
| Package 1 Length | 2.8 in (7 cm) |
| Package weight(Lbs) | 3.62 lb(US) (1.64 kg) |
| SCC14 | 10731304279706 |

Contractual warranty

| | |
|-----------------------------|----|
| Warranty (in months) | 24 |
|-----------------------------|----|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

| | |
|--|---|
| Total lifecycle Carbon footprint | 143 kg CO2 eq. |
| Carbon footprint of the manufacturing phase [A1 to A3] | 8 kg CO2 eq. |
| Carbon footprint of the distribution phase [A4] | 0.1 kg CO2 eq. |
| Carbon footprint of the installation phase [A5] | 0.7 kg CO2 eq. |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 132 kg CO2 eq. |
| Carbon footprint of the end-of-life phase [C1 to C4] | 3 kg CO2 eq. |
| Environmental Disclosure | Product Environmental Profile |

Use Better



Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | No |
| Packaging without single use plastic | No |
| SCIP Number | 1cdb2fed-a06f-4574-913d-8df8e70936b2 |
| EU RoHS Directive | Compliant |
| REACH Regulation | Free of Substances of Very High Concern above the threshold |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| Halogen content performance | Product contains halogen above thresholds |

Use Longer



Lifetime extension

| | |
|--------|----|
| Repair | No |
|--------|----|

Use Again



Repack and remanufacture

| | |
|-------------------------------|--|
| Recyclability potential, in % | 30 |
| Circularity Profile | End of Life Information |
| Take-back | No |
| WEEE Label |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |