

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 9K series, 0U, 17.3kW, 208V, 20 C13/C15, 12 C19/C21 outlets

APDU9966

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	5.97 ft (1.82 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Complementary

Input Voltage	208 V 3 phase
Height	72.2 in (1833 mm)
Width	4.4 in (111 mm)
Output Voltage	208 V
Depth	3.0 in (76 mm)
Net Weight	30.9 lb(US) (14 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 60 A 3P+PE
Mounting Mode	Rack-mounted
Communication Port Protocol	SNMP Redfish
Line Rated Current	48 A
Max line current	48 A
Input current limits	60 A
Load Capacity	17300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	20C13/C15 12C19/C21
Communication Network Type	10/100/1000BASE-T

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed FCC part 15 class A
Standards	IEC 62368-1
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304356332
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	84.6 in (214.9 cm)
Package 1 Width	4.4 in (11.2 cm)
Package 1 Length	8.7 in (22.1 cm)
Package weight(Lbs)	44.004 lb(US) (19.96 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	8 526 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	111 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.5 kg CO2 eq.
Carbon footprint of the installation phase [A5]	3 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	8 404 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	8 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	71
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	No

Image of product / Alternate images

Alternative

