

APC Smart-UPS, Line Interactive, 1000VA, Lithium-ion, Rack/Tower, 2U, 120V, 6x NEMA 5-15R outlets, SmartConnect Port+Network Card, Short Depth, AVR

SMTL1000RM2UCNC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock
Main	
Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	800 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R
Number of rack unit	2U
Cable length	8 ft (2.4 m)
Battery Type	Li-lon (Lithium Ion)
Provided equipment	Rack Mounting brackets Rack Mounting support rails Screw Washer USB cable Ethernet patch cable
Range of Product	Smart-UPS

Complementary

Communication port type	SmartConnect Ethernet port
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Extendable Run Time	0
Typical recharge time	3 h
Battery design life	810 year(s)
Battery Charge Power (Watts)	79 W rated

General

product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

color	Black with silver front bezel
Height	3.39 in (8.6 cm)
Width	17.24 in (43.8 cm)
Depth	12.52 in (31.8 cm)
Net Weight	35.9 lb(US) (16.3 kg)
Mounting preference	Lower
Mounting Mode	Rack-mounted
USB compatible	Yes

Input

•	
Input protection type	Circuit breaker
Efficiency at full load	75154 V adjustable 82144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Crest factor	3:1
Harmonic distortion	Less than 5%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	800 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	NOM
Equipment protection policy	Lifetime: \$150000

Environmental

Acoustic level	41 dBA
Online Thermal Dissipation	135 Btu/h
Operating altitude	010000 ft

Ambient air temperature for operation	32104 °F (040 °C)
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage altitude	025000 ft (0.00000000007620.0000000000 m)
IP degree of protection	IP20
Relative Humidity	095 % non-condensing
Storage Relative Humidity	095 % non-condensina

Communications & Management

Audible Alarm	Audible and visible alarms
control panel	Multi-function LCD status and control console
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping
	response time: m

Ordering and shipping details

GTIN 731304435464

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.02 in (22.9 cm)
Package 1 Width	1.86 in (4.72 cm)
Package 1 Length	22.99 in (58.4 cm)
Package 1 Weight	41.006 lb(US) (18.6 kg)

Contractual warranty

Warranty 5 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1278
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration

Use Again

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Removable battery	User replaceable	
Take-back	No	