

Product data sheet

Specifications



APC Smart-UPS Ultra On-Line,
5000VA, Lithium-ion, Rack/Tower
2U, 208V, 2 L6-20R + 2 L6-30R
NEMA outlets, Network Card,
Extended runtime, W/rail kit

SRTL5KRM2UT

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V AC 1 phase
Other Input Voltages	240 V
Input Connection Type	NEMA L6-30P
Efficiency at full load	180...275 V adjustable (half load)
Input Frequency	40 - 70 Hz auto-sensing
Output voltage	208 V AC 1 phase
Other Output Voltages	240 V
Rated power in W	4900 W
rated power in VA	4900 VA
output connection type	2 NEMA L6-20R 2 NEMA L6-30R
Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	4900 VA
Max Configurable Power (Watts)	4900 W
Topology	On-Line
Waveform Type	Sine wave
Full load runtime	00:05:00 4900 W
Half load runtime	00:12:00 2450 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Li-Ion (Lithium Ion) internal included
Emergency Power Off (EPO)	Yes
Free slots	0
Alarm	Audible and visible alarms : prioritized by severity



Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

UPS connectivity	Serial port USB port Embedded network management card 3
Surge energy rating	1260 J
Number of rack unit	2U
Cable length	10.007 ft (3.05 m)
Number of cables	1
color	Silver grey
Height	3.4 in (86 mm)
Width	17.008 in (432 mm)
Depth	27.6 in (701 mm)
Net Weight	64.4 lb(US) (29.2 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal Vertical
Mounting mode	Rack-mounted with included kit
Provided equipment	1 CD (software and documentation) Network cable Rack Mounting brackets
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	High density
Redundant	No
Range of Product	Smart-UPS Ultra
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	ENERGY STAR V2.0 (USA)
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dBA
Heat dissipation	1047 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Li-Ion (Lithium Ion)
Battery Voltage	180 V
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	1.5 h
RBC Quantity	1
Battery Life	5...10 year(s)
Battery Charge Power (Watts)	600 W rated

Ordering and shipping details

GTIN	731304435730
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	15.4 in (39.2 cm)
Package 1 Width	23.03 in (58.5 cm)
Package 1 Length	38.7 in (98.4 cm)
Package weight(Lbs)	84.9 lb(US) (38.5 kg)
SCC14	10731304435730

Contractual warranty

Warranty (in months)	60
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	9 340 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 990 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	11 kg CO2 eq.
Carbon footprint of the installation phase [A5]	14 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	7 275 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	50 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	5ee38369-4dfb-4636-ab65-b08aa3242891
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold



Energy efficiency

Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
Product contributes to saved and avoided emissions	Yes

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	53
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes

Image of product / Alternate images

Alternative



