

Product data sheet

Specifications



APC NetShelter AV, Server Rack Enclosure, 24U, 10-32 Threaded Rails, Black, 1199H x 600W x 806D mm

AR3814

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation	Feature-rich enclosure specifically for the professional A/V market and optimized for cable management, power distribution, and airflow management.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	24U
Provided equipment	Baying hardware Documentation CD Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Height	47.2 in (1199 mm)
Width	23.6 in (600 mm)
Depth	32.5 in (825 mm)
Net Weight	180.38 lb(US) (81.82 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	27.6 in (702.1 mm)
Rack Width	19"
Permanent permissible load	2250 lb(US) (1020.6 kg) dynamic 3000 lb(US) (1360.8 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	731304284109
-------------	--------------

Returnability	No
----------------------	----

Country of origin	TH
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
------------------------------	---

Package 1 Height	52.2 in (132.7 cm)
-------------------------	--------------------

Package 1 Width	40.5 in (102.9 cm)
------------------------	--------------------

Package 1 Length	29.5 in (74.9 cm)
-------------------------	-------------------

Package weight(Lbs)	209.4 lb(US) (95 kg)
----------------------------	----------------------

Contractual warranty

Warranty (in months)	60
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	333 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	318 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	8 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



