

# Product data sheet

Specifications



## APC NetShelter Rack PDU Advanced, Switched, 3Phase, 8.6kW, 208V 30A, 48 Outlets, L21-30P

APDU10351SW

! To be discontinued

! Discontinued on: Sep 3, 2025

### Overview

Lead time Usually in Stock

### Main

Color Black

Product or Component Type PDU

PDU Type Switched

Cord length 5.9 ft (1.8 m)

### Complementary

Input Voltage 208 V 3 phase

Height 70.08 in (1780 mm)

Width 2.2 in (56 mm)

Output Voltage 208 V

Depth 3.0 in (75 mm)

Net Weight 20.7 lb(US) (9.4 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type NEMA L21-30P

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication Port Protocol 1000BASE-T  
10/100BASE-T

Line Rated Current 24 A

permissible voltage 200...240 V

Input current limits 30 A

Load Capacity 8600 VA

Input Frequency 50/60 Hz

Outlet type and quantity 24 C13/C15/C19/C21  
24C13/C15

### Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Product Certifications</b>	TAA compliance BAA compliance
<b>Standards</b>	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B
<b>IP Degree of Protection</b>	IP44
<b>Ambient Air Temperature for Operation</b>	23...140 °F (-5...60 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0...15240 m)

## Ordering and shipping details

<b>GTIN</b>	731304439806
<b>Country of origin</b>	US

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	78.0 in (198 cm)
<b>Package 1 Width</b>	4.6 in (11.6 cm)
<b>Package 1 Length</b>	8.2 in (20.8 cm)
<b>Package weight(Lbs)</b>	27.3 lb(US) (12.4 kg)

## Contractual warranty

<b>Warranty (in months)</b>	36
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	2 046 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	69 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 970 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No

Image of product / Alternate images

Alternative

---

### 4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21

### Multiple color options available











