

# Product data sheet

Specifications



## APC NetShelter Rack PDU Advanced, Switched Metered Outlet, 1Phase, 5.0kW, 208V 30A, 40 Outlets, L6-30P

APDU10151SM

⚠ To be discontinued

⚠ Discontinued on: Sep 3, 2025

## Overview

Lead time Usually in Stock

## Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched metered outlet
Cord length	9.8 ft (3.0 m)

## Complementary

Input Voltage	208 V 1 phase
Height	58.7 in (1490 mm)
Width	2.2 in (56 mm)
Output Voltage	208 V
Depth	3.0 in (75 mm)
Net Weight	17.2 lb(US) (7.8 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Communication Port Protocol	1000BASE-T 10/100BASE-T
Line Rated Current	24 A
Acceptable Input Voltage	200...240 V
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz
Outlet type and quantity	20 C13/C15/C19/C21 20C13/C15

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Product Certifications</b>	TAA compliance BAA compliance
<b>Standards</b>	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B
<b>IP Degree of Protection</b>	IP44
<b>Ambient Air Temperature for Operation</b>	23...140 °F (-5...60 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0...15240 m)

## Ordering and shipping details

<b>GTIN</b>	731304439783
<b>Country of origin</b>	US

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	67.7 in (172 cm)
<b>Package 1 Width</b>	4.6 in (11.6 cm)
<b>Package 1 Length</b>	8.2 in (20.8 cm)
<b>Package weight(Lbs)</b>	21.6 lb(US) (9.8 kg)

## Contractual warranty

<b>Warranty (in months)</b>	36
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	1 969 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	176 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 787 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Nej

Image of product / Alternate images

Alternative

---

Multiple color options available



4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21



Deploy IT gear faster



4-in-1 outlet to simplify planning



Alternating phase and color-coded outlets



Fast, flexible mounting

Handle high density loads



More outlets and kW



Slim design to fit more PDUs in one rack

Avoid downtime



60° operating temperature



Environmental sensors



Live swap display





