

# Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, North America

AP8706S-NA

### **Overview**

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

### Main

Product or Component Type	Power cord	
Input Connection Type	IEC 60320 C14	
Cable length	6 ft (1.8 m)	
Number of cables	Č.	

## **Physical**

Color	Black	
Height	9.45 in (24 cm)	
Width	2.95 in (7.5 cm)	
Depth	2.17 in (5.5 cm)	
Net Weight	2.98 lb(US) (1.35 kg)	
Mounting preference	No preference	
Mounting Mode	Not rack-mountable	

## Input

Max line current	10 A	
Input current limits	10 A	

## **Output**

Max current draw	10 A
Number of power socket outlets	1 IEC 60320 C13
Cord Length	6 ft (1.8 m)

#### Conformance

Product Certifications	CSA
	UL Listed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environmental**

Ambient air temperature for operation	32221 °F (0105 °C)	
Relative Humidity	2080 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13221 °F (-25105 °C)	
Storage Relative Humidity	2080 %	
Storage altitude	050000 ft (0.000000000015240.000000000 m)	

# Ordering and shipping details

**GTIN** 731304294405

# **Packing Units**

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.45 in (24 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	2.95 in (7.5 cm)
Package 1 Weight	2.98 lb(US) (1.35 kg)

# **Contractual warranty**

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	425
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

EU RoHS Directive	Compliant	
REACh Regulation	REACh Declaration	
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov	

#### **Use Again**

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Halogen content performance	Product contains halogen above thresholds	
Take-back	Yes	