

Product data sheet

Specifications



APC DIN Rail - Panel Mount UPS with High Temp Battery 500VA 120V

SUA500PDR-H

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Efficiency at full load	75...154 V adjustable 82...144 V
Number of input connectors	1 Hard Wire 3-wire (1PH+N+G)
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V
Rated power in W	325 W
rated power in VA	500 VA
Output connector type	Hard Wire 3-wire (H N + E) for 1 zone(s)
Harmonic distortion	Less than 5%
Maximum configurable power in VA	500 VA
Max Configurable Power (Watts)	325 W
Topology	Line Interactive
Waveform Type	Sine wave
Efficiency at full load	94 % full load)
Output Frequency (sync to mains)	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains

Complementary

Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Surge energy rating	540 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m
Height	5.8 in (148 mm)
Width	14.3 in (362 mm)
Depth	6.7 in (171 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	25.31 lb(US) (11.48 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Provided equipment	CD with software Documentation CD Installation guide Smart UPS signalling RS-232 cable
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	UL Recognized
Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Ambient Air Temperature for Storage	23...131 °F (-5...55 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %
Acoustic level	55 dBA
Online Thermal Dissipation	90 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Battery Type	Lead-Acid battery
Extendable Run Time	0
Included Battery Modules	1
Battery Slots Empty	1
Typical recharge time	2 h
RBC Quantity	1
Battery Life	3...5 year(s)
Replacement battery	APCRBC136 
Battery Charge Power (Watts)	60 W rated

Ordering and shipping details

Category	09305-INDUSTRIAL UPS
Discount Schedule	IUPS
GTIN	731304794493
Returnability	No

Country of origin	PH
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	11.7 in (29.7 cm)
Package 1 Width	18.9 in (48.1 cm)
Package 1 Length	11.7 in (29.7 cm)
Package weight(Lbs)	29.3 lb(US) (13.3 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	498 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	191 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	5 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	295 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	7 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	B2b22a56-41f2-497e-9ea6-cf093b3b8bd3
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes