

# Product data sheet

Specifications



APC Back UPS, 1200VA/650W,  
Tower, 120V, 8x NEMA 5-15R  
outlets, USB Type A + C Ports,  
User Replaceable Battery

BVK1200M2

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage 120 V AC 1 phase

Input Connection Type NEMA 5-15P

Input protection type Circuit breaker

Plug standard NEMA  
5-15P

Efficiency at full load 108...150 V

Output voltage 120 V AC 1 phase

Rated power in W 650 W

rated power in VA 1200 VA

output connection type 8 NEMA 5-15R

USB Charging Port None

Maximum configurable power in  
VA 1200 VA

Max Configurable Power (Watts) 650 W

Topology Line Interactive

Waveform Type Stepped approximation to a sinewave

Output Frequency (sync to mains) 50/60 Hz

## Complementary

Battery Capacity 9 Ah

Battery Size Lead-acid internal included

Control panel LED Status display with On Line : On Battery

Emergency Power Off (EPO) Yes

UPS connectivity None

Surge energy rating 350 J

Cable length 4.9 ft (1.5 m)

Number of cables 1

color Black

Height 7.5 in (190 mm)

Width 5.5 in (140 mm)



Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	15.4 in (390 mm)
Net Weight	17.0 lb(US) (7.7 kg)
Mounting preference	No preference
USB compatible	No
Mounting mode	Tower
Range of Product	Back-UPS
Product or Component Type	Uninterruptible power supply (UPS)

## Environment

IP degree of protection	IP20 CSA C22.2 No 107.3
-------------------------	-------------------------

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a> 
Efficiency	<a href="#">View Efficiency Graph</a> 
Battery Type	Lead-Acid battery
Battery Voltage	12 V
Battery graph comments	Curve fit to measured runtime data. All measurements taken with new, fully charged batteries, at typical environmental conditions, with no electrical input and balanced resistive load (PF = 1.0) output.
Typical recharge time	6 h

## Ordering and shipping details

GTIN	731304449140
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	11.7 in (29.7 cm)
Package 1 Width	9.3 in (23.5 cm)
Package 1 Length	19.5 in (49.5 cm)
Package weight(Lbs)	19.2 lb(US) (8.7 kg)

## Contractual warranty

Warranty (in months)	36
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	310 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	83 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.9 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	225 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.8 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	408bc71c-8e0f-47fa-8853-2385b53226ec
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Reference contains Substances of Very High Concern above the threshold</a>



### Energy efficiency

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Recyclability potential, in %	62
Circularity Profile	<a href="#">End of Life Information</a>
Removable battery	User replaceable
Take-back	Yes

Technical Illustration

Dimensions

---



Offer Marketing Illustration

Product benefits / Features

---



Offer Marketing Illustration

Product benefits / Features

---



Offer Marketing Illustration

Product benefits / Features

---



Offer Marketing Illustration

Product benefits / Features

---

**Ideal power protection  
for your home office**



Wi-Fi Modem / Router



PC desktop computer



PC monitor




Network-Attached storage



Offer Marketing Illustration

Product benefits / Features


---



Offer Marketing Illustration

Product benefits / Features

---



Offer Marketing Illustration

Product benefits / Features

---

**Stay connected in case of power outages**

Enjoy uninterrupted internet connection for your entertainment, smart home, and security devices.



Power backup for your Wi-Fi Modem / Router


Offer Marketing Illustration

Product benefits / Features

---

### AVR : Automatic Voltage Regulation

Voltage fluctuations put your devices at risk. AVR instantly corrects variances in incoming voltage, ensuring stable and consistent power to your connected devices.



#### Benefits of AVR



Increased battery life



Protection against system crash



Protection against data loss