

Product data sheet

Specifications



APC Smart-UPS 3kVA RM 120V SHIPBOARD

SMX3000RMX93

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V AC 1 phase
Other Input Voltages	100 V
Input Connection Type	NEMA L5-30P
Efficiency at full load	70...153 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Other Output Voltages	100 V
Rated power in W	2700 W
rated power in VA	2880 VA
output connection type	3 NEMA 5-15R
Harmonic distortion	Less than 5%
Maximum configurable power in VA	2880 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	2-4 ms
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Lead-acid internal included
Free slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
UPS connectivity	Serial port USB port
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m
Number of rack unit	4U
Cable length	8 ft (2.4 m)
Number of cables	1
color	Black

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	17.008 in (432 mm)
Width	7.008 in (178 mm)
Depth	19.02 in (483 mm)
Net Weight	85.19 lb(US) (38.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	1
USB compatible	Yes
Mounting mode	Rack-mounted
Provided equipment	User's documentation in electronic format
Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	TAA compliance
Redundant	No
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	BSMI
Equipment protection policy	Lifetime : \$150000
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %
Acoustic level	55 dBA
Online Thermal Dissipation	276 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)

Replacement battery	APCRBC117 
Battery Charge Power (Watts)	245 W rated

Ordering and shipping details

GTIN	731304433668
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	13.0 in (33 cm)
Package 1 Width	23.1 in (58.8 cm)
Package 1 Length	26.1 in (66.3 cm)
Package weight(Lbs)	105.006 lb(US) (47.63 kg)

Contractual warranty

Warranty (in months)	36
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	3 241 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 543 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	18 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 675 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	58
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

