Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

APC 3000VA Filter - MARINE

High availability, ruggedized power protection for shipboard and other transportation

SURT023M



Overview

Presentation

applications.	
Lead time	Usually in Stock
Main	
Main Input Voltage	208 V
	220 V
	230 V
	240 V
Product or Component Type	Filter
Main Output Voltage	200 V
	208 V
	220 V
	230 V
	240 V
Other Output Voltage	208 V
	220 V
	230 V
	240 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Cable length	8 ft (2.4 m)
Number of cables	1

Environment

Provided equipment

Ambient air temperature for operation	32131 °F (055 °C)
Relative Humidity	095 %
Operating altitude	010000 ft
Ambient Air Temperature for Storage	-13167 °F (-2575 °C)
Storage Relative Humidity	095 %
Storage altitude	050000 ft (0.0000000000 15240.0000000000 m)

Installation guide Mounting Hardware User Manual

Physical

Color	Black
Height	1.73 in (4.4 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	17.01 in (43.2 cm)
Depth	10.98 in (27.9 cm)
Net Weight	11.22 lb(US) (5.09 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	4763 Hz	
Line Rated Current	16 A	
Permissible voltage	100240 V	
Max line current	16 A	
Input current limits	16 A	
Load Capacity	3000 VA	

Output

Max current draw	16 A	
Number of power socket outlets	1 IEC 60320 C19	
Number of power socket outlets	1	
Protection Type	Without circuit breaker	
Cord Length	8 ft (2.4 m)	

Conformance

Product Certifications DNV

Ordering and shipping details

GTIN 731304284697

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.99 in (7.6 cm)
Package 1 Width	15.00 in (38.1 cm)
Package 1 Length	22.01 in (55.9 cm)
Package 1 Weight	14.02 lb(US) (6.36 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes