

Product data sheet

Specifications



Rack PDU 2G, Metered-by-Outlet, ZeroU, 5.7kW, 208V, (21) C13 & (3) C19

AP8461

Overview

Presentation	APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection. Current metering provides real-time remote monitoring of connected loads. Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Lead time	Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Metered outlet
Cord length	5.9 ft (1.8 m)
Provided Equipment	CAN Port Terminator Installation guide Rack Mounting brackets Safety guide Serial configuration cable

Complementary

Input Voltage	208 V 3 phase
Height	70 in (1778 mm)
Width	2.2 in (56 mm)
Output Voltage	208 V
Depth	2.008 in (51 mm)
Net Weight	18.10 lb(US) (8.21 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L21-20P
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Line Rated Current	16 A
Max line current	20 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input current limits	20 A
Load Capacity	5700 VA
Input Frequency	50/60 Hz
Outlet type and quantity	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product Certifications	cUL Listed UL Listed VCCI Class A
Standards	FCC Part 15 class A ICES-003
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304317593
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	80.2 in (203.7 cm)
Package 1 Width	4.6 in (11.7 cm)
Package 1 Length	6.4 in (16.3 cm)
Package weight(Lbs)	23.10 lb(US) (10.48 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	1 960 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	188 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 766 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold
Halogen content performance	Product contains halogen above thresholds

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

