

Product data sheet

Specifications



APC NetShelter Soundproof, 17U, Server Rack Enclosure, 120V, Maple [TAA]

AR4017A

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually Ships within 2 Weeks

Main

Product or Component Type	Rack enclosure
Main Input Voltage	100...120 V
Input Connection Type	NEMA 5-15P
output connection type	10 NEMA 5-15R
Number of rack unit	17U
Cable length	11.98 ft (3.65 m)
Number of cables	1
Provided equipment	Casters

Physical

Height	39.6 in (1005 mm)
Width	29.5 in (750 mm)
Depth	44.5 in (1130.4 mm)
Net Weight	317.5 lb(US) (144 kg)
Color	Maple
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Mounting position	Horizontal
Maximum Mounting Depth	32.7 in (830 mm)
Minimum Mounting Depth	27.2 in (690 mm)
Rack Width	19"
Permanent permissible load	1851.9 lb(US) (840 kg) static

Input

Input Frequency 50/60 Hz

Output

PDU Type Basic

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	EIA-310D
-----------	----------

Ordering and shipping details

GTIN	731304621737
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	44.09 in (112 cm)
Package 1 Width	32.3 in (82 cm)
Package 1 Length	47.2 in (120 cm)
Package weight(Lbs)	414.5 lb(US) (188 kg)

Compliance

Compliance	TAA Compliant
------------	---------------

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	660 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	630 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	16 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	14 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	5aa5ed58-9f72-49f2-ad76-720ad4129c6e
EU RoHS Directive	Compliant
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative







