

Product data sheet

Specifications



APC Smart-UPS, Lithium-Ion, 2200VA, 120V with SmartConnect Port, Network Card and L5-20R, No Battery

SMTL2K2R2CLNC-NB

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V AC 1 phase
Output voltage	120 V AC 1 phase
Rated power in W	1920 W
rated power in VA	2200 VA
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1920 W
Topology	Line Interactive

Complementary

Battery Size	Li-Ion (Lithium Ion) external sold separately
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
UPS connectivity	Serial port USB port SmartConnect port Pre-installed network management card 3
Number of rack unit	0U
Mounting Mode	Not rack-mountable
Mounting mode	Rack-mounted with included kit
Redundant	No
Range of Product	Smart-UPS
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	ENERGY STAR V2.0 (USA)
Storage altitude	0...25000 ft (0...7620 m)

Batteries & Runtime

Battery Type	Li-Ion (Lithium Ion)
Extendable Run Time	0

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

GTIN	731304451242
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1

Contractual warranty

Warranty (in months)	60
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	1 300 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	447 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	5 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	847 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold



Energy efficiency



ENERGY STAR®

ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

