

# Rack PDU 2G, Switched, ZeroU, 15A, 100-120V, (8) 5-15

AP8931

## Overview

Presentation

APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.

Lead time

Usually in Stock

## Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Switched	
Cord length	10 ft (3.05 m)	
Number of cables	1	
Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide	

# Complementary

Input Voltage	100 V 120 V	
Height	38.90 in (98.8 cm)	
Width	2.17 in (5.5 cm)	
Output Voltage	100 V 120 V	
Depth	1.81 in (4.6 cm)	
Net Weight	9.17 lb(US) (4.16 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	NEMA 5-15P	
Mounting Mode	Not rack-mountable	
Rack units	0U	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting position	Vertical
Line Rated Current	12 A
Permissible voltage	100120 V
Input current limits	15 A
Load Capacity	1440 VA
Input Frequency	50/60 Hz
Outlet type and quantity	8 NEMA 5-15R

# **Environment**

Product Certifications	cUL Listed PSE UL Listed	
Standards	FCC Part 15 class A ICES-003 UL 60950-1	
Ambient air temperature for operation	23140 °F (-560 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

# Ordering and shipping details

GTIN 731304307525

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	44.53 in (113.1 cm)	
Package 1 Width	4.26 in (10.83 cm)	
Package 1 Length	6.30 in (16 cm)	
Package 1 Weight	11.07 lb(US) (5.02 kg)	

# **Contractual warranty**

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1670
Environmental Disclosure	Product Environmental Profile

## **Use Better**

Materials and Substances	
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
᠃ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

## Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	Yes
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes