



RGB LED Desktop Stereo Computer Speakers

3.5 mm Stereo Audio Aux Connection, USB-A Powered, Color-LED Lighting, Set of Two Speakers, Black

Part No.: [168359](#)

EAN-13: 0766623168359 | UPC: 766623168359

PC Speakers - wired 3.5 mm Aux and USB power for gaming and more - crystal-clear dual-channel sound with simple setup and atmospheric color-LED lighting

The Manhattan RGB LED Desktop Stereo Computer Speakers offer simple setup and controls for a convenient, enjoyable listening experience. This set of two PC speakers is compact and moveable but offers rich, powerful sound. They make a great upgrade from your built-in notebook or monitor speakers.

Simple and quick connection

Just plug the single USB cable into a USB-A port to supply the speakers with power. The port can be on a PC, laptop, or Mac®, but you can also plug it into a USB wall charger. This flexibility lets you put the speakers either on your desk (as traditional PC speakers), on a bookshelf, or wherever you want sound. Rotary volume control with an on/off switch is conveniently located on the front of the right speaker.

Full immersion with ambient light

Create just the right atmosphere in dark rooms while you game or play videos and music. The four color-changing RGB LED ambilight circles - two in each

speaker - are synchronized in a constant, non-configurable loop.

Features:

- Powerful stereo speakers for table or shelf with rich, clear, high-quality sound
- 3.5 mm stereo audio aux plug on built-in 1.8 m (6 ft.) cable for wired music playback
- USB-A plug on built-in 1.8 m (6 ft.) cable for power supply
- Color-changing RGB LED light circles for immersive atmosphere with games, music and movies
- Dual external speakers improve stereo separation and sound field
- Great upgrade from built-in notebook or monitor speakers
- Convenient integrated rotary volume control and on/off switch
- Plug-and play from any source with an aux-out such as a PC, laptop, Chromebook[™], MacBook[®], gaming console, tablet, smartphone, MP3 player, iPod[®] and more
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- RoHS
- FCC
- UKCA

General

- Frequency response: 30 Hz - 15000 Hz
- Power output: 5.0 W total (2 x 2.5 W)
- Power input: DC 5.0 V / 0.5 A via USB-A
- Input sensitivity: 960.0 mV
- Signal-to-noise ratio (S/N): ≤88 dB
- Impedance: 4 Ohm

Connections

- One 3.5 mm stereo audio aux, male
- One USB-A 4-pin, male

Physical

- Speaker dimensions, each (L x W x H): 78 x 105 x 174 mm (3.07 x 4.13 x 6.85 in.)
- Aux cable length: 1.8 m (6 ft.)

- USB cable length: 1.8 m (6 ft.)
- Cable length connecting speakers: 1 m (3.3 ft.)
- Total net weight: 640 g (1.41 lbs.)
- Total gross weight: 690 g (1.52 lbs.)

System Requirements

- Compatible with all versions of Windows[®], macOS[®], iPadOS[®], Linux[®], Chrome OS[™], iOS[®] and Android[™]

Operating Environment

- Operation temperature: 0 - 40°C (32 - 104°F)
- Storage temperature: -20 - 65°C (-4 - 149°F)
- Humidity (noncondensing): 20 - 90%

Package Contents

- RGB LED Desktop Stereo Computer Speakers
- Instructions

Please note: LEDs cannot be turned off.



