

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 9K series, 0U, 11.5kW, 200-240V, 21 C13/C15 and 3 C19/C21 outlets

APDU9981NA3

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	5.97 ft (1.82 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Complementary

Input Voltage	415 V 3 phase
Height	70.5 in (1791 mm)
Width	2.2 in (55 mm)
Output Voltage	208 V 240 V
Depth	1.8 in (46 mm)
Net Weight	15.4 lb(US) (7 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 20 A 3P+N+PE
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	16 A
Max line current	20 A
Input current limits	20 A
Load Capacity	11500 VA
Input Frequency	50/60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Outlet type and quantity	21C13/C15 3C19/C21
Communication Network Type	10/100/1000BASE-T

Environment

Product Certifications	cUL Listed FCC part 15 class A PSE
Standards	UL 62368-1
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304404255
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	78.8 in (200.2 cm)
Package 1 Width	4.5 in (11.4 cm)
Package 1 Length	6.5 in (16.5 cm)
Package weight(Lbs)	19.73 lb(US) (8.95 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	1 246 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	50 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 192 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	No
--------	----

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

