

Product data sheet

Specifications



APC Smart-UPS SRT 5kVA, 208V, Tower w/o kit, 8x 5-20R, 4x L6-20R, 2x L6-30R, 1x L14-30R NEMA, w/transfo 208/240V to 120V

SRT5KXLT-5KTF

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V AC 1 phase
Other Input Voltages	240 V
Input Connection Type	NEMA L6-30P
Efficiency at full load	100...275 V adjustable (half load)
Input Frequency	40 - 70 Hz auto-sensing
Output voltage	120 V 1 phase 208 V 1 phase
Other Output Voltages	240 V
Rated power in W	4800 W
rated power in VA	5000 VA
output connection type	8 NEMA 5-20R 4 NEMA L6-20R 2 NEMA L6-30R 1 NEMA L14-30R
Bypass type	Internal Bypass (Automatic and Manual)
Harmonic distortion	Less than 2%
Maximum configurable power in VA	5000 VA
Max Configurable Power (Watts)	4800 W
Topology	On-Line
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Lead-acid internal included
Emergency Power Off (EPO)	Yes
Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
UPS connectivity	Serial port USB port Embedded network management card 3

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surge energy rating	480 J
Cable length	10.007 ft (3.05 m)
color	Black
Height	17.008 in (432 mm)
Width	10.2 in (259 mm)
Depth	28.3 in (719 mm)
Net Weight	248.00 lb(US) (112.49 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical
Mounting mode	Rack-mounted with included kit
Provided equipment	CD with software Documentation CD Installation guide Integrated network management Removable support feet Temperature Probe
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	High density
Redundant	No
Range of Product	Smart-UPS On-Line
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	ENERGY STAR V2.0 (USA)
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	55 dBA
Heat dissipation	1047 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Lead-Acid battery
Battery Voltage	192V

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	1.5 h
RBC Quantity	1
Battery Life	3...5 year(s)
Replacement battery	APCRBC140 
Battery Charge Power (Watts)	556 W rated

Ordering and shipping details

GTIN	731304739814
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	26.7 in (67.8 cm)
Package 1 Width	38.6 in (98 cm)
Package 1 Length	24.02 in (61 cm)
Package weight(Lbs)	281.99 lb(US) (127.91 kg)

Contractual warranty

Warranty (in months)	36 UPS 24 Battery
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	12 317 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	1 627 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	18 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	10 656 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	16 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Energy efficiency



ENERGY STAR®

ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	65
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes

Image of product / Alternate images

Alternative

