

APC Smart-UPS On-Line, 3kVA, Tower, 208V, 2x L6-20R+1x L6-30R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit

SRT3000XLT

Overview

Lead time Usually in Stock

Main

wain		
Main Input Voltage	208 V	
Product or Component Type	Uninterruptible power supply (UPS)	
Other Input Voltage	240 V	
Main Output Voltage	208 V	
Other Output Voltage	240 V	
Kw Rating	2700 W	
Rated power in VA	3000 VA	
Input Connection Type	NEMA L6-20P	
output connection type	2 NEMA L6-20R 1 NEMA L6-30R	
Cable length	10 ft (3.05 m)	
Number of cables	1	
Provided equipment	CD with software Documentation CD Installation guide Removable support feet USB cable Warranty card	
Range of Product	Smart-UPS On-Line	

Batteries & Runtime

Run Time	View Runtime Graph ☐	
Efficiency	View Efficiency Graph ☐	
Battery Type	Lead-Acid battery	
Battery Voltage	96V	
Extendable Run Time	1	
Included Battery Modules	1	
Typical recharge time	3 h	
RBC Quantity	1	
Battery life	35 year(s)	
Replacement battery	APCRBC152 ☐	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Battery Charge Power (Watts) 165 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
Topology	Double Conversion Online

Physical

color	Black
Height	17.01 in (43.2 cm)
Width	3.35 in (8.5 cm)
Depth	25.00 in (63.5 cm)
Net Weight	69.005 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical

Input

Efficiency at full load	100275 V adjustable (half load)	
Input Frequency	40 - 70 Hz auto-sensing	

Output

Bypass type	Internal Bypass (Automatic and Manual)	
Crest factor	3:1	
Harmonic distortion	Less than 2%	
Maximum configurable power in VA	3000 VA	
Max Configurable Power (Watts)	2700 W	
Wave type	Sine wave	
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains	
Additional information	Configurable for 208 or 240 nominal output voltage	

Conformance

Product Certifications	ENERGY STAR V2.0 (USA)	
------------------------	------------------------	--

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	773 Btu/h

Operating altitude	010000 ft	
Ambient air temperature for operation	32104 °F (040 °C)	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	
IP degree of protection	IP20	
Relative Humidity	095 % non-condensing	
Storage Relative Humidity	095 % non-condensing	

Communications & Management

Emergency Power Off (EPO)	Yes	
Free slots	1	
Alarm	Audible and visible alarms : prioritized by severity	

Surge Protection and Filtering

Surge energy rating 340 .

Ordering and shipping details

GTIN 731304317685

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.69 in (24.6 cm)
Package 1 Width	34.29 in (87.1 cm)
Package 1 Length	23.58 in (59.9 cm)
Package 1 Weight	81.00 lb(US) (36.74 kg)

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4978
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	4282bd22-a353-4f82-bb5c-97bbd7f1d1e9
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
᠃ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes