

Product data sheet

Specifications



APC NetShelter Basic Rack PDU, 0U/1U, 100-240V/20A, 220-240V/ 16A, 7 C13 and 2 C19 outlet

AP6120A

Overview

Lead time Usually in Stock

Main

Product or Component Type PDU
PDU Type Basic
Provided Equipment Installation guide
Safety guide

Complementary

Input Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Height 1.7 in (44 mm)

Width 15.3 in (388 mm)

Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Depth 3.7 in (93 mm)

Net Weight 3.44 lb(US) (1.56 kg)

Mounting Location Front
Rear

Mounting preference No preference

Input Plug Type IEC 60320 C20

Mounting Mode Not rack-mountable

Rack units 1U

USB compatible No

Mounting position Horizontal

Line Rated Current 16 A

permissible voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Load Capacity 2300 VA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input Frequency	50/60 Hz
------------------------	----------

Outlet type and quantity	7 IEC 60320 C13 2 IEC 60320 C19
---------------------------------	------------------------------------

Environment

Product Certifications	cUL Listed CE EAC IRAM PSE UL Listed VDE
-------------------------------	--

Ordering and shipping details

GTIN	731304327851
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Nbr. of units in pkg.	1
------------------------------	---

Package 1 Height	8.3 in (21 cm)
-------------------------	----------------

Package 1 Width	3.0 in (7.6 cm)
------------------------	-----------------

Package 1 Length	17.2 in (43.6 cm)
-------------------------	-------------------

Package weight(Lbs)	4.45 lb(US) (2.02 kg)
----------------------------	-----------------------

SCC14	50731304327856
--------------	----------------

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	3 734 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	3 726 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Recyclability potential, in %	45
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



