

# Product data sheet

Specifications



APC NetShelter Basic Rack PDU,  
0U, 1 phase, 3.3kW, 100-240V  
20A or 200-240V 16A, 13 C13  
outlets, C20 inlet

AP6020A

## Overview

**Presentation** Reliable rack power distribution designed to increase manageability and efficiency in the data center. The output and input connections are (13) C13. Real-time remote monitoring of connected loads. User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.

**Lead time** Usually in Stock

## Main

**Color** Black

**Product or Component Type** PDU

**PDU Type** Basic

**Provided Equipment** Installation guide  
Safety guide

## Complementary

**Input Voltage** 100 V  
120 V  
200 V  
208 V  
230 V  
240 V

**Height** 15.3 in (388 mm)

**Width** 1.7 in (44 mm)

**Depth** 3.7 in (93 mm)

**Net Weight** 3.3 lb(US) (1.5 kg)

**Mounting Location** Front  
Rear

**Mounting preference** Lower

**Input Plug Type** IEC 60320 C20

**Mounting Mode** Not rack-mountable

**Rack units** 1U

**USB compatible** No

**Mounting position** Horizontal

**Line Rated Current** 16 A

**permissible voltage** 100...240 V

**Max line current** 20 A

**Input current limits** 20 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	13 IEC 60320 C13

---

## Environment

---

Product Certifications	cUL Listed CE EAC IRAM PSE UL Listed VDE
------------------------	--

## Ordering and shipping details

---

GTIN	731304327806
------	--------------

## Packing Units

---

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	17.2 in (43.6 cm)
Package 1 Width	3.0 in (7.6 cm)
Package 1 Length	8.3 in (21 cm)
Package weight(Lbs)	4.45 lb(US) (2.02 kg)
SCC14	10731304327803

## Contractual warranty

---

Warranty (in months)	24
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	3 734 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	3 726 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>
Halogen content performance	Product contains halogen above thresholds

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture


Recyclability potential, in %	45
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

