ProductSheet

HP ScanJet Enterprise Flow 7000 s3 Sheet-feed Scanner (L2757A)

Give your office high-volume scanning performance. Recommended for 7,500 pages per day.

Give your office high-volume scanning performance. Easily download software—including Kofax VRS 5.1 Professional[4]—that helps you save time and capture confidently. Achieve scan speeds up to 75 ppm/150 ipm.[1] Recommended for 7,500 pages per day.



Fast, smooth scanning—even unattended
Capture entire documents with one-pass duplex scanning up to 150 ipm black-and-white and color.[1]

Peak workflow performance. Smarter scanning.
Identify new devices and gain insight into scanning with HP Web Jetadmin remote discovery and monitoring.[3]

Professional-grade scanning that helps save time
Save time and simplify complex scan jobs with HP Scan Premium.



Featuring

One-pass duplex scanning

7,500-page duty cycle

HP EveryPage, ultrasonic sensor

80-page ADF

HP Scan Premium

Scan originals in a variety of sizes and weights

Specifications

Scanner advanced features	Auto exposure, Auto threshold, Auto detect color, Background smooth/removal, Remove Noise, Auto detect size, Straighten content, Enhance content, Multi-streaming, Auto feed, Multi-feed detection sensor, Auto orient, Multi-color dropout, Channel color dropout, Edge erase, Resize page, Delete blank page, Merge pages, Hole fill, Digital stamps, Metadata capture, PDF permissions, Document separation (Blank page, Barcode)
Connectivity, standard	USB 2.0 and USB 3.0 (Hi-Speed)
Software included	HP WIA scan driver, HP TWAIN scan driver (32-bit and 64-bit), HP Scan Premium, HP Scanner Tools Utility, EMC ISIS driver, Kofax VRS Pro
Compatible Operating Systems	OS X El Capitan 10.11, Microsoft® Windows®10, 8, 7, XP
Sustainable impact specifications	RoHS compliance, HP GSE standard
Energy star certified	Yes
Ecolabels	ENERGY STAR® 3.0 certified
Digital sending standard features	Scan to PC, Scan to USB Drive
Scan file format	For text & images: ePub 3.0, HTML 4.0, Excel file format (*.xls, *.xlsx), PowerPoint file format (*.pptx), Word (*.docx), WordPerfect (*.wpd), searchable PDF, JPEG, PNG, BMP, TIFF, Text (.txt), Rich Text (rtf), XML and XPS
Scan input modes	Two scan modes (simplex/duplex) on front-panel for HP Scan Premium in Win OS and third parties applications via TWAIN, ISIS and WIA
Scan technology	CMOS CIS
Scanner type	Sheetfed
Minimum dimensions (W x D x H)	310 x 198 x 190 mm
Minimum dimensions (W x D x H)	12.20 x 7.79 x 7.48 in
Weight	3.8 kg
Weight	8.4 lb
Power consumption	6.7 watts (ready), 0.9 watts (sleep), 0.1 watts (off), 0.1 watts (auto-off)[2]
Power supply type	External Power Adapter
What's in the box	HP ScanJet Enterprise Flow 7000 s3 Sheet feed Scanner; Installation guide, Support flyer, Warranty guide; Power cord; USB cable; Power Adapter
Manufacturer Warranty	One-year bench limited warranty whole unit replacement, phone and Web support included. Warranty may vary by country as required by law. Go to http://www.hp.com/support to learn about HP world-class service and support options in your region.

Top Recommended Displays, Accessories and Services

HP ScanJet Maintenance Kits

HP ScanJet 5000 s4/7000 s3 Roller Replacement Kit	L2756A

Messaging Footnotes

[1] Scan speed measured at 300 dpi (black-and-white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, computer performance, and application software.

[3] HP Web Jetadmin is available for download at no additional charge at http://www.hp.com/go/webjetadmin. Support for the HP ScanJet Enterprise Flow 7000 s3 available mid-November, 2016.

[4] Expected availability for Kofax VRS 5.1 Professional is November 1, 2016

Technical Specifications Footnotes

[2] Power requirements are based on the country/region where the scanner is sold. Do not convert operating voltages. This will damage the scanner and void the product warranty.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.