

# Product data sheet

Specifications



## APC NetShelter Switched Rack PDU, 2U, 30A, 208V, 16 C13 outlet

AP7911B

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Overview

Lead time Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	11.98 ft (3.65 m)
Number of cables	1
Provided Equipment	Documentation CD Installation guide Rack Mounting brackets

### Complementary

Input Voltage	200 V 208 V 230 V
Height	3.5 in (89 mm)
Width	17.5 in (445 mm)
Output Voltage	208 V
Depth	10 in (254 mm)
Net Weight	13.93 lb(US) (6.32 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
Mounting Mode	Rack-mounted
Rack units	2U
Mounting position	Horizontal
Line Rated Current	24 A
permissible voltage	200...240 V
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz
Outlet type and quantity	16 IEC 60320 C13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

<b>Product Certifications</b>	cUL Listed CSA Industry Canada PSE UL Listed
<b>Standards</b>	FCC Part 15 class A ICES-003 UL 60950
<b>Ambient Air Temperature for Operation</b>	32...113 °F (0...45 °C)
<b>Relative Humidity</b>	0...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13...149 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	0...95 %
<b>Storage altitude</b>	0...50000 ft (0...15240 m)

## Ordering and shipping details

<b>Category</b>	80230-IG SEBA TO SEUSA
<b>Discount Schedule</b>	BMS1
<b>GTIN</b>	731304331605
<b>Returnability</b>	No
<b>Country of origin</b>	PH

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	5.7 in (14.6 cm)
<b>Package 1 Width</b>	20.2 in (51.4 cm)
<b>Package 1 Length</b>	20.2 in (51.4 cm)
<b>Package weight(Lbs)</b>	18.43 lb(US) (8.36 kg)

## Contractual warranty

<b>Warranty (in months)</b>	24
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	2 005 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	46 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 954 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

### Use Longer

#### Lifetime extension

Repair	No
--------	----

### Use Again

#### Repack and remanufacture


Recyclability potential, in %	71
Circularity Profile	<a href="#">End of Life Information</a>
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

