

AXIS W120 Body Worn Camera

For live streaming, and tracking – your way

AXIS W120 Body Worn Camera is a fully connected wearable camera featuring built-in LTE/4G, Wi-Fi[®] and Bluetooth[®], which enables direct streaming with AXIS Body Worn Live. It delivers clear audio with noise suppression and exceptional image quality. Electronic image stabilization guarantees the highest possible forensic value. The camera also delivers detailed status information via its LCD screen. AXIS W120 is robust, easy-to-use and features the KlickFast mounting system. It offers up to 15 hours of battery time and can be charged on-the-go with any USB-C[®] charger. Recording can be activated automatically, and the location of the camera is continuously recorded thanks to the built-in GNSS receiver.

- > [Live streaming via LTE/4G](#)
- > [Location tracking](#)
- > [Always sharp images](#)
- > [Excellent sound quality](#)
- > [Multiple layers of encryption](#)



AXIS W120 Body Worn Camera

Camera

Image sensor

1/2.9" progressive scan RGB CMOS
Sensitivity: 0.1 lux

Lens

Focal length, 2.3 mm
Horizontal field of view: 137°
Vertical field of view: 76°
Fixed iris, F2.1

Shutter speed

1/20000 s to 1/25 s with 50 Hz
1/20000 s to 1/30 s with 60 Hz

Video

Video compression

H.264 (MPEG-4 Part 10/AVC) High Profile

Resolution

1920x1080, 1280x720

Frame rate

25 fps at 50 Hz
30 fps at 60 Hz

WDR

WDR

Image settings

Electronic image stabilization (720p), barrel distortion correction

Video streaming

Axis Zipstream for body worn

Audio

Audio encoding

AAC-LC
One channel: 48 kHz, 128 kbps
Two channels (optimized for post-processing mode):
48 kHz, 2x128 kbps

Audio input/output

Built-in dual microphones

Functionality

Voice enhancement

Approvals

Supply chain

TAA compliant

EMC

EN 55032 Class B, EN 55035, EN 61000-6-1,
EN 61000-6-2, EN 61000-6-3, EN 61000-6-4,
Canada: ICES-3(B)/NMB-3(B)
USA: FCC Part 15 Subpart B Class B

Safety

CAN/CSA C22.2 No. 62368-1 ed. 3,
IEC/EN/UL 62368-1 ed. 3, RCM AS/NZS 62368.1:2018,
IS 13252

Environment

IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14,
IEC 60068-2-78, IEC/EN 60529 IP67
MIL-STD-810H (Method 501.7, 503.7, 505.7, 509.7,
512.6, 516.8)

Wireless

AS/CA S042.1, AS/CA S042.4, AS/NZS 4268, EN 50566,
EN 300328, EN 300440, EN 301893, EN 303413,
EN 301489-1, EN 301908-1, EN 301489-17,
EN 301489-19, EN 301489-52, EN 301908-13,
EN 62209-2, FCC Part 2 Subpart J,
FCC Part 15 Subpart C, FCC Part 15 Subpart E,
FCC Part 22 Subpart H, FCC Part 24 Subpart E,
FCC Part 27, FCC Part 90, IFT, RSS-102, RSS-130,
RSS-132, RSS-133, RSS-139, RSS-140, RSS-247,
RSS-Gen, WPC

Cybersecurity

ETSI EN 303 645, BSI IT Security Label

Cybersecurity

Edge security

Software: Signed OS, AES-XTS-Plain64 256bit encryption
Hardware: Secure boot, Axis Edge Vault with Axis device ID, signed video, secure keystore (CC EAL6+ certified hardware protection of cryptographic operations and keys). CJIS compliant encrypted internal storage (AES256)

Network security

IEEE 802.1X (EAP-TLS, PEAP-MSCHAPv2), IEEE 802.1AR, HTTPS/HSTS¹, TLS v1.2/v1.3¹
WPA/WPA2-PSK, WPA/WPA2-Enterprise (EAP-TLS, EAP-PEAP/MSCHAPv2)

Documentation

Axis body worn cameras – system security white paper, available at axis.com/learning/white-papers
Axis Vulnerability Management Policy
Axis Security Development Model
AXIS OS Software Bill of Material (SBOM)
To download documents, go to axis.com/support/cybersecurity/resources
To read more about Axis cybersecurity support, go to axis.com/cybersecurity

General

Battery

Li-ion, 3600 mAh
Up to 15 hours operating time in 720p²
Up to 13.5 hours operating time in 1080p²
Up to 29 hours in standby mode³

Storage

64 GB non-volatile memory, up to 30 hours of recorded video
AES256 encryption standard

Throughput

Camera to system controller: 100 Mbit/s

Recording

Configurable audio and video prebuffer 0, 15, 30, 60, 90, and 120 seconds
Configurable audio and video postbuffer 0, 10, 30, and 60 seconds

Positioning system

GPS, GLONASS, Galileo, BeiDou

Location

Track, start and end

Sensor

3-axis gyroscope and accelerometer, compass

User interface

Color IPS TFT display, 0.96 inch, 160x80 pixels
Status indicators
Audio and vibration feedback

Wireless interface

Bluetooth® 5.1 Low Energy and Classic
Bluetooth profile: None
Wi-Fi® 5 a/b/g/n/ac @ 2.4 GHz, 5 GHz
LTE (US): Bands B2, B4, B5, B12, B13, B14, B25, B26, B66, B71 CAT4
LTE (EU): Bands B1, B3, B7, B8, B20, B28 CAT4

Casing

IP67-rated
Plastic casing
Drop tested up to 2 m

Color

Black NCS S 9000-N
White NCS S 1002-B

Mounting

Klick Fast™ System

Connectors

Pogo pin pads
USB (for Axis accessories and charging using a cable with a USB Type-C® connector)

SIM card

Nano-SIM (4FF)

Operating conditions

Temperature: -20 °C to 50 °C (-4 °F to 122 °F)
Maximum temperature (intermittent, <1 hour): 55 °C (131 °F)
Humidity: 10–100% RH (condensing)

Charging conditions

Temperature: 0 °C to 40 °C (32 °F to 104 °F)
Charging time:
<6.5 hours in 0–15 °C (32–59 °F)
<4 hours in 15–30 °C (59–86 °F)
<5.5 hours in 30–40 °C (86–104 °F)
Humidity: 5–95% RH (non-condensing)

1. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).
2. With pre-buffer, and fewer than 500 charge cycles.
3. Without pre-buffer, and including 1 hour of recording per charge in 720p, and fewer than 500 charge cycles.

Storage conditions

Temperature (< 3 months): -20 °C to 45 °C (-4 °F to 113 °F)

Temperature (> 3 months): 23 °C to 27 °C (73 °F to 81 °F)

Optimal temperature: 25 °C (77 °F)

Humidity: 5–95% RH (non-condensing)

Dimensions

For the overall product dimensions, see the dimension drawing in this datasheet.

Weight

200 g (0.44 lb)

Optional accessories

Klick Fast™ System for Body worn camera mounts

AXIS TW1200 Body Worn Mini Bullet Sensor

AXIS TW1201 Body Worn Mini Cube Sensor

AXIS TW1906 Battery Replacement

AXIS Body Worn Assistant app for Android, iOS

For more accessories, see axis.com/bodyworn

Warranty

The product, including the battery, is subject to a 3-year warranty period, in accordance with the terms and conditions stated in Axis 5 Year Limited Hardware Warranty available on axis.com/warranty ("3-year Warranty Period").

In addition to the terms and conditions in the Axis 5 Year Limited Hardware Warranty, the warranty doesn't cover battery degradation if the battery has undergone more than 500 charge cycles, if the camera has been used or stored in temperatures outside the specifications in the datasheet, or if the instructions in the product's user manual haven't been followed.

Replacement of the battery during the 3-year Warranty Period carried out by any other party than Axis (or an RMA partner on behalf of Axis) will void the main item's warranty. Contact Axis Support or your reseller for battery- or service-related matters.

Sustainability

Substance control

RoHS in accordance with EU RoHS Directive 2011/65/EU/ and EN 63000:2018

REACH in accordance with (EC) No 1907/2006. For SCIP UUID, see echa.europa.eu

Environmental responsibility

axis.com/environmental-responsibility

Axis Communications is a signatory of the UN Global Compact, read more at unglobalcompact.org

Dimension drawing

