Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Power Cord Kit (6 EA), Locking, C19 TO C20, 0.6M (2FT), Red

AP8712SX340

Overview

Lead time Usually in Stock

Main

Product or Component Type	Power cord	
Input Connection Type	IEC 60320 C20	
Cable length	2 ft (0.6 m)	
Number of cables	¢.	

Physical

Color	Red	
Height	11.81 in (30 cm)	
Width	2.36 in (6 cm)	
Depth	2.56 in (6.5 cm)	
Net Weight	2.47 lb(US) (1.12 kg)	
Mounting preference	No preference	
Mounting Mode	Not rack-mountable	

Input

Max line current	16 A
Input current limits	16 A

Output

Max current draw	16 A	
Number of power socket outlets	s 1 IEC 60320 C19	
Cord Length	2 ft (0.6 m)	

Conformance

Product Certifications	CCC	
	CSA	
	PSE	
	UL Listed	
	VDE	

Environmental

Ambient air temperature for	32167 °F (075 °C)
operation	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Relative Humidity	2080 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13167 °F (-2575 °C)	
Storage Relative Humidity	2080 %	
Storage altitude	0 50000 ft (0 000000000 15240 000000000 m)	

Ordering and shipping details

GTIN	731304329411	
Country of origin	CN	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	11.81 in (30 cm)	
Package 1 Width	2.56 in (6.5 cm)	
Package 1 Length	2.36 in (6 cm)	
Package 1 Weight	2.47 lb(US) (1.12 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	352
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
[⋄] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes