

Product data sheet

Specifications



APC Smart-UPS, Line Interactive,
1500VA, Lithium-ion, Rackmount
3U, 120V, 6x NEMA 5-15R outlets,
SmartConnect Port+SmartSlot,
Short Depth, AVR, LCD

SMTL1500RM3UC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	1350 W
Rated power in VA	1440 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R
Number of rack unit	3U
Cable length	8 ft (2.4 m)
Battery Type	Li-Ion (Lithium Ion)
Provided equipment	Installation guide Rack Mounting support rails USB cable
Range of Product	Smart-UPS

Complementary

Communication port type	SmartConnect Ethernet port SmartSlot
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Typical recharge time	3 h
Battery design life	8...10 year(s)
Battery Charge Power (Watts)	154 W rated

General

product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

color	Black with silver front bezel
Height	5.16 in (13.1 cm)
Width	17.24 in (43.8 cm)
Depth	11.89 in (30.2 cm)
Net Weight	43.0 lb(US) (19.5 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted
USB compatible	Yes

Input

Input protection type	Circuit breaker
Efficiency at full load	75...154 V adjustable 82...144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Crest factor	3 : 1
Graph start point	68
Harmonic distortion	Less than 5%
Maximum configurable power in VA	1440 VA
Max Configurable Power (Watts)	1350 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	NOM
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	45 dBA
Online Thermal Dissipation	135 Btu/h
Operating altitude	0...10000 ft

Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...25000 ft (0.0000000000...7620.0000000000 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Audible Alarm	Audible and visible alarms
control panel	Multi-function LCD status and control console
Free slots	1
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304339632
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.98 in (27.9 cm)
Package 1 Width	17.64 in (44.8 cm)
Package 1 Length	22.99 in (58.4 cm)
Package 1 Weight	50.0009 lb(US) (22.68 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1297
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	C151e0e4-d5aa-4595-a297-c593b8808426

Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes