



## Lead the way with this sophisticated next-gen AI PC

Leave a lasting impression with the brilliantly designed HP EliteBook Ultra G1i Next Gen AI PC. This new signature of success mirrors your executive style and unifies your decision making with AI and advanced conferencing features that take your strategy to action.



### **HP Recommends Windows 11 Pro**

Summarize and rewrite content, get relevant recommendations, and stay organized with Microsoft Copilot.[10]

### **Intel® powers next-gen AI PCs**

Free up time to focus on what matters with the latest 48 TOPS capable Intel® Core™ Ultra processor.[2,3]

### **AI-powered assistance**

Unlock new capabilities and eliminate routine tasks with the HP EliteBook Ultra G1i Next Gen AI PC.[6]

## Featuring

### **HP recommends Windows 11 Pro for business**

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [4]

### **Intel® powers next Gen AI PCs**

Free up time to focus on what matters with the latest Intel® Core™ Ultra processor purposely built for the next era of AI software. Three compute engines manage AI workloads, help improve video conferencing and allow for advanced content creation. [5]

### **Fast and efficient wireless LAN**

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7. [7]

### **Browse confidently**

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [8]

### **HP Sure Sense**

Malware is evolving rapidly beyond traditional antivirus capabilities. Protect your PC against never-before-seen attacks with HP Sure Sense, which combines behavioral analysis with advanced AI techniques to provide exceptional protection. [9]

## Specifications

<b>Operating system</b>	Windows 11 Pro
<b>Product color</b>	Atmosphere blue
<b>Processor family</b>	Intel® Core™ Ultra 5 processor
<b>Processor</b>	Intel® Core™ Ultra 5 228V (up to 4.5 GHz Max Turbo frequency, 8 MB L3 cache, 8 cores, 8 threads) <sup>[6,7]</sup>
<b>Memory</b>	32 GB LPDDR5x-8533 MT/s (onboard)
<b>Internal Storage</b>	512 GB PCIe® NVMe™ SSD
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® Arc™ Graphics
<b>Display</b>	35.6 cm (14") diagonal, 2.8K (2880 x 1800), OLED, touch, IPS, BrightView, 400 nits, 100% DCI-P3
<b>Display</b>	14" diagonal, 2.8K (2880 x 1800), OLED, touch, IPS, BrightView, 400 nits, 100% DCI-P3 <sup>[9,10,11,12]</sup>
<b>Display size (diagonal)</b>	35.6 cm (14")
<b>Display size (diagonal)</b>	14"
<b>Audio</b>	Audio by Poly Studio, quad stereo speakers, dual microphones enhanced by AI noise reduction
<b>Dimensions (W x D x H)</b>	31.37 x 21.72 x 0.9 cm (front); 31.37 x 21.72 x 1.21 cm (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Dimensions (W x D x H)</b>	12.35 x 8.55 x 0.36 in (front); 12.35 x 8.55 x 0.48 in (rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
<b>Weight</b>	Starting at 1.19 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Weight</b>	Starting at 2.63 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
<b>Keyboard</b>	Full-size, backlit, atmosphere blue keyboard with HP Imagepad
<b>Pointing device</b>	Haptic trackpad with multi-touch gesture support
<b>Input devices</b>	Accelerometer; Gyroscope; Thermal sensor
<b>Ports</b>	1 USB Type-A 10Gbps signaling rate (charging); 1 stereo headphone/microphone combo jack; 3 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1) <sup>[33]</sup> <i>(Cables are not included.)</i>
<b>Wireless</b>	Intel® Wi-Fi 7 BE201 (2x2) and Bluetooth® 5.4 wireless card
<b>Power</b>	65 W USB Type-C™ adapter <sup>[14]</sup>
<b>Battery type</b>	HP Long Life 6-cell, 64 Wh Li-ion polymer
<b>Ecolabels</b>	TCO Certified
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Sustainable impact specifications</b>	Low halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Ocean-bound plastic in speaker enclosure(s); 90% recycled metal
<b>UPC number</b>	198990731711
<b>Manufacturer Warranty</b>	1-year warranty and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to <a href="http://www.hp.com/support/batterywarranty/">http://www.hp.com/support/batterywarranty/</a> for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <a href="http://www.hp.com/go/cpc">http://www.hp.com/go/cpc</a> .

## Top Recommended Displays, Accessories and Services

---

### Power Adapters

HP 110W USB-C Laptop Charger	8B3Y2AA
HP 110W USB-C Laptop Charger	8B3Y2UT
HP 65W USB-C LC Power Adapter	1P3K6AA
HP USB-C 65W Laptop Charger	671R3AA
HP USB-C 65W Laptop Charger	671R3UT

## Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors.

[4] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[5] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Features and software that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Performance varies by use, configuration, and other factors. ISV solutions are sold separately and may require a subscription and NPU.

[6] HP AI Companion is available preloaded on select HP next gen AI PCs or is available for download from the Microsoft store and requires a HP next gen AI PC with a NPU supporting 40-60 TOPS and requires Windows 11. Perform requires account set up within 30 days of PC boot or enrollment through the HP AI Companion app. Some features require customer upload of local data. Five (5) library 100MB limit each, supported files may vary and at launch include pdf, .txt, .docx files.

[7] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[8] HP Sure Click requires Windows 10 and higher. See [https://bit.ly/2PrLT6A\\_SureClick](https://bit.ly/2PrLT6A_SureClick) for complete details.

[9] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

[10] Microsoft Copilot requires Windows 11. Some features require an NPU. Timing of feature delivery and availability varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

## Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[9] 2K content required to view 2K images.

[10] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[11] Actual brightness will be lower with touchscreen.

[12] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[14] Availability may vary by country.

[33] USB 20Gbps speed is not available with Thunderbolt™ 4.

---

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Thunderbolt and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

