

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 12U, Shock Packaging, Black, 658H x 600W x 1070D mm [TAA]

AR3103SP

Overview

Presentation An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices. Shock pallet and shock packaging simplify IT "rack and stack" for equipment integrators.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 12U

Provided equipment Casters
Door
Key(s)
Leveling feet
Pallet ramps
Reusable packaging
Roof
Side Panels

Physical

Height 25.9 in (658 mm)

Width 23.6 in (600 mm)

Depth 42.1 in (1070 mm)

Net Weight 130.007 lb(US) (58.97 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 36.3 in (920.8 mm)

Minimum Mounting Depth 7.5 in (191 mm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 600 lb(US) (272.2 kg) dynamic
600 lb(US) (272.2 kg) static

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Ordering and shipping details

GTIN	731304347682
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	37.8 in (96 cm)
Package 1 Width	48.8 in (124 cm)
Package 1 Length	29.5 in (75 cm)
Package weight(Lbs)	253.5 lb(US) (115 kg)

Compliance

Compliance	TAA Compliant BAA Compliant via COTS
-------------------	---

Contractual warranty

Warranty (in months)	60
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	404 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	385 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	10 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	9 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



