

HP DesignJet HD Pro 2 44-in MFP (2QX51E)



High-definition graphics 44-in MFP for technical and graphics applications—fast and secure

Quickly print and scan maps, drawings, POP graphics/displays, posters, photos, and more with the HP DesignJet HD Pro 2 44-in MFP. See high-quality results delivered efficiently and securely.



PRECISE—Excellent reproduction with CCD technology

Reproduce colors with excellent accuracy with CCD technology that enables high-quality color scanning/copying.

FAST—HD scanner designed to streamline workflows

Scan fast—up to 13 inches (33 cm) per second in either color or monochrome.

SECURE—Protect your work and your information

Protect printers/data from unauthorized access with HP Secure Boot, whitelisting, 500 GB encrypted hard disk.

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print, copy, scan
Connectivity, standard	Printer: Gigabit Ethernet (1000Base-T), Hi-Speed USB 2.0 certified interface for direct printing from USB flash drive; Scanner: Gigabit Ethernet (1000Base-T), USB 3.1 gen 1 (3+1) and USB 2.0 (1) rear
Software included	Printer drivers, HP Click, HP Web Jetadmin, HP JetAdvantage Security Manager, HP DesignJet Utility including HP Color Center, HP MPS, integrated software with scan and copy enhancement features
Scan file format	PDF, PDF/A, TIFF, JPEG, JPEG2000, DWF, CALS (B&W), multi-page PDF generation
Scan input modes	File, email, USB, HDD, network folder, FTP, print
Scanner type	CCD scanning technology and LED-based illumination system
Minimum dimensions (W x D x H)	Printer: 1802 x 695 x 998 mm; Scanner: 1530 x 930 x 1660 mm
Minimum dimensions (W x D x H)	Printer: 70.9 x 27.4 x 39.3 in; Scanner: 60 x 37 x 65 in
Weight	Printer: 96 kg; Scanner: 71 kg
Weight	Printer: 211 lb; Scanner: 157 lb
Power consumption	Printer: <100 W (printing); <32 W (ready); <0.3 W (<6.5 W with embedded Digital Front End) (sleep); 0.1 W (off); Scanner: 130 W (scanning); 39 W (ready); <1 W (sleep)
Environmental certification	Printer: ENERGY STAR; ErP; WEEE; RoHS (EU, China, Korea, India); REACH; EPEAT; Scanner: ENERGY STAR; WEEE; RoHS (EU, China, Korea, India); REACH; EPEAT
What's in the box	Printer: HP DesignJet Z6dr 44-in PostScript Printer with V-Trimmer, printheads, introductory ink cartridges, printer stand and media bin, spindle, 3-in core adapter, quick reference guide, setup poster, power cord; Scanner: HP HD Pro 2 42-in Scanner, stand, touchscreen (panel PC), quick reference guide, media guides, setup poster, maintenance sheet, copy/scan software, documentation software, Ethernet cable, USB cable, power cords
Manufacturer Warranty	One-year limited hardware warranty

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

