

Product data sheet

Specifications



APC Smart-UPS, Line Interactive, 750VA, Lithium-ion, Rackmount 2U, 230V, 6x IEC C13 outlets, SmartConnect Port+SmartSlot, Short Depth, AVR, LCD

SMTL750RMI2UC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V AC 1 phase
Other Input Voltages	220 V 240 V
Input Connection Type	IEC 60320 C14
Input protection type	Circuit breaker
Efficiency at full load	151...302 V adjustable 160...286 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	230 V AC 1 phase
Other Output Voltages	220 V 240 V
Rated power in W	600 W
rated power in VA	750 VA
output connection type	6 IEC 60320 C13 2 IEC Jumpers
Crest factor	3 : 1
Harmonic distortion	Less than 5%
Maximum configurable power in VA	750 VA
Max Configurable Power (Watts)	600 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery Size	Li-Ion (Lithium Ion) internal included
Control panel	Multi-function LCD status and control console
Free slots	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Alarm	Alarm when on battery : distinctive low battery alarm
UPS connectivity	Serial port USB port SmartConnect port Available expansion slot
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use
Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m
Number of rack unit	2U
color	Black with silver front bezel
Height	3.4 in (86 mm)
Width	17.2 in (438 mm)
Depth	12.5 in (318 mm)
Net Weight	34.0 lb(US) (15.4 kg)
Mounting preference	Lower
Mounting Mode	Rack-mounted
USB compatible	Yes
Mounting mode	Rack-mounted with included kit
Provided equipment	USB cable Ethernet patch cable Rack Mounting brackets Screw Washer Rack Mounting support rails
Additional specification	Cloud-enabled monitoring
Redundant	No
Range of Product	Smart-UPS
Product or Component Type	Uninterruptible power supply (UPS)

Environment

Product Certifications	C-tick CE EAC UK PSTI
Standards	EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...25000 ft (0...7620 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing
Acoustic level	41 dBA
Online Thermal Dissipation	135 Btu/h

Operating altitude	0...10000 ft
--------------------	--------------

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery Type	Li-Ion (Lithium Ion)
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0
Typical recharge time	3 h
Battery design life	8...10 year(s)
Battery Charge Power (Watts)	50 W rated

Ordering and shipping details

GTIN	731304407966
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.02 in (22.9 cm)
Package 1 Width	18.6 in (47.2 cm)
Package 1 Length	23.0 in (58.4 cm)
Package weight(Lbs)	41.006 lb(US) (18.6 kg)

Contractual warranty

Warranty (in months)	60
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	433 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	218 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	199 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	12 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	8519b6fb-f7a9-44f8-be44-5dee68362126
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold



Energy efficiency

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	51
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

