

Product data sheet

Specifications



APC NetShelter 6U Wallmount Rack Enclosure Cabinet, Single Hinged, Switch Depth, Unassembled

AR106

Overview

Presentation	Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack is packaged unassembled for smaller storage and delivery and takes up to 60% less space than assembled alternatives. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top/bottom mounted. Top/bottom feature knockouts 1/2U of mounting space for accessories. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 6U Wall mount cabinet, 8.9 to 12.9 inches mounting depth, 200lb weight capacity, 19" rack width, ships unassembled, 5 year APC warranty.
---------------------	---

Lead time	Usually in Stock
------------------	------------------

Main

Product or Component Type	Rack enclosure
----------------------------------	----------------

Number of rack unit	6U
----------------------------	----

Physical

Height	14.02 in (356 mm)
---------------	-------------------

Width	23.6 in (599 mm)
--------------	------------------

Depth	15.7 in (400 mm)
--------------	------------------

Net Weight	20.70 lb(US) (9.39 kg)
-------------------	------------------------

Color	Black
--------------	-------

Mounting Support	Wall
-------------------------	------

Mounting preference	No preference
----------------------------	---------------

Mounting Mode	Not rack-mountable
----------------------	--------------------

Maximum Mounting Depth	12.9 in (328.9 mm)
-------------------------------	--------------------

Minimum Mounting Depth	8.9 in (226.1 mm)
-------------------------------	-------------------

Rack Width	19"
-------------------	-----

Permanent permissible load	200 lb(US) (90.7 kg) static
-----------------------------------	-----------------------------

Conformance

Standards	EIA-310E
------------------	----------

Ordering and shipping details

GTIN	731304317265
-------------	--------------

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	11.5 in (29.3 cm)
Package 1 Width	19.09 in (48.5 cm)
Package 1 Length	27.09 in (68.8 cm)
Package weight(Lbs)	32.10 lb(US) (14.56 kg)

Contractual warranty

Warranty (in months)	60
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	51 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	49 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



