

# Wall Mount, Security and Environmental Appliance, NetBotz, 756 with PoE Injector

NBWL0756

#### Overview

Presentation	The NetBotz Room Monitor 755 provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes where IT rack space is unavailable.
Lead time	Usually in Stock

#### Main

Product or Component Type	Industrial rack PC
Range of Product	Nothotz

#### **General**

Camera Frame Rate	Up to 30fps
APC Universal Sensors	0-5V
Supported	Door contact
	Dry Contact
	Fluid Spot Leak
	Humidity
	Smoke
	Temperature
	Vibration
Number of Universal Sensor	4

## Ports

## **Physical**

Color	Black
Mounting Mode	Not rack-mountable

#### **Environmental**

Ambient air temperature for operation	32113 °F (045 °C)
Operating altitude	09842.52 ft (03000 m)
Ambient Air Temperature for Storage	5149 °F (-1565 °C)
Storage altitude	0.000000000049212.6 ft (015000 m)

#### **Communications & Management**

Communication Network Type 10/100/1000BASE-T

### Ordering and shipping details

**GTIN** 731304371915

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.76 in (19.72 cm)
Package 1 Width	18.52 in (47.04 cm)
Package 1 Length	28.48 in (72.35 cm)
Package 1 Weight	9.802 lb(US) (4.446 kg)

# Contractual warranty

Warrant	ty	2 Years



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
Use Again	

○ Repack and remanufacture	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No