

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 0U, 5.0kW, 200V and 208V, 30A, 21 C13/C15 and 3 C19/C21 outlets

APDU9941

Overview

Lead time Usually in Stock

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	9.8 ft (3 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Complementary

Input Voltage	208 V 200 V
Height	72.008 in (1829 mm)
Width	2.2 in (55 mm)
Output Voltage	200 V 208 V
Depth	1.8 in (46 mm)
Net Weight	18.7 lb(US) (8.5 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	4992 VA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input Frequency	50/60 Hz
Outlet type and quantity	21C13/C15 3C19/C21
Communication Network Type	10/100/1000BASE-T

Environment

Product Certifications	cUL Listed FCC part 15 class A PSE
Standards	ICES-003
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304356264
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	80.3 in (204 cm)
Package 1 Width	4.9 in (12.4 cm)
Package 1 Length	6.5 in (16.5 cm)
Package weight(Lbs)	22.05 lb(US) (10 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 642 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	56 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2 580 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	71
Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



