

# Product data sheet

Specifications



## APC NetShelter Switched Rack PDU, 9K series, 0U, 20A, 208V, 21 C13/C15 and 3 C19/C21, L620 Cord

APDU9959NA3

### Overview

Lead time Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

### Complementary

Input Voltage	200 V 208 V
Height	70.7 in (1797 mm)
Width	2.2 in (55 mm)
Output Voltage	208 V 200 V
Depth	1.8 in (46 mm)
Net Weight	12.37 lb(US) (5.61 kg)
Mounting Location	Side
Mounting preference	No preference
Input Plug Type	IEC 60320 L6-20P
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication Port Protocol	SNMP Redfish
Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	21C13/C15 3C19/C21

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Communication Network Type	10/100/1000BASE-T
----------------------------	-------------------

## Environment

---

Product Certifications	cUL Listed FCC part 15 class A PSE
Standards	IEC 62368-1
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

---

## Ordering and shipping details

---

GTIN	731304356301
------	--------------

## Packing Units

---

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	78.8 in (200.2 cm)
Package 1 Width	4.5 in (11.4 cm)
Package 1 Length	6.5 in (16.5 cm)
Package weight(Lbs)	17.33 lb(US) (7.86 kg)

---

## Contractual warranty

---

Warranty (in months)	36
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	1 550 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	44 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	1 502 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	<a href="#">Compliant By Exemption</a>
REACH Regulation	<a href="#">Reference contains Substances of Very High Concern above the threshold</a>

### Use Longer

#### Lifetime extension

Repair	No
--------	----

### Use Again

#### Repack and remanufacture


Recyclability potential, in %	71
Circularity Profile	<a href="#">End of Life Information</a>
Removable battery	Yes
Take-back	Nej
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

