

Product data sheet

Specifications



APC NetShelter Soundproof, 32U, Server Rack Enclosure, 120V, Maple [TAA]

AR4032A

Overview

Lead time Usually Ships within 2 Weeks

Main

Product or Component Type Rack enclosure

Main Input Voltage 100...120 V

Input Connection Type NEMA 5-15P

output connection type 10 NEMA 5-15R

Number of rack unit 32U

Cable length 11.98 ft (3.65 m)

Number of cables 1

Provided equipment Casters

Physical

Height 65.9 in (1675 mm)

Width 29.5 in (750 mm)

Depth 44.5 in (1130.4 mm)

Net Weight 476.2 lb(US) (216 kg)

Color Maple

Mounting preference No preference

Mounting Mode Not rack-mountable

Mounting position Horizontal

Maximum Mounting Depth 32.7 in (830 mm)

Minimum Mounting Depth 27.2 in (690 mm)

Rack Width 19"

Permanent permissible load 3306.9 lb(US) (1500 kg) static

Input

Input Frequency 50/60 Hz

Output

PDU Type Basic

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	EIA-310D
-----------	----------

Ordering and shipping details

GTIN	731304621768
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	70.4 in (178.7 cm)
------------------	--------------------

Package 1 Width	32.3 in (82 cm)
-----------------	-----------------

Package 1 Length	47.2 in (120 cm)
------------------	------------------

Package weight(Lbs)	573.2 lb(US) (260 kg)
---------------------	-----------------------

Compliance

Compliance	TAA Compliant
------------	---------------

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	912 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	871 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	22 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	19 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	95
Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative







