

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced, Switched, 3Phase, 11kW 400V 16A or 11.5kW 415V 20A, 42 Outlets, IEC309

APDU10250SW

! To be discontinued

! Discontinued on: Sep 3, 2025

Overview

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Switched

Cord length 5.9 ft (1.8 m)

Complementary

Input Voltage 415 V 3 phase
400 V 3 phase

Height 58.7 in (1490 mm)

Width 2.2 in (56 mm)

Output Voltage 240 V

Depth 3.0 in (75 mm)

Net Weight 15.9 lb(US) (7.2 kg)

Mounting Location Side

Mounting preference No preference

Input Plug Type IEC 60309 20 A 3P+N+PE

Mounting Mode Rack-mounted

Rack units 0U

Mounting position Vertical

Communication Port Protocol 1000BASE-T
10/100BASE-T

Line Rated Current 16 A

permissible voltage 200...240 V
346...415 V

Input current limits 20 A

Load Capacity 11500 VA

Input Frequency 50/60 Hz

Outlet type and quantity 21 C13/C15/C19/C21
21C13/C15

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	UKCA TAA compliance BAA compliance
Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
IP Degree of Protection	IP44
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

GTIN	731304439691
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	67.7 in (172 cm)
Package 1 Width	4.6 in (11.6 cm)
Package 1 Length	8.2 in (20.8 cm)
Package weight(Lbs)	20.3 lb(US) (9.2 kg)

Contractual warranty

Warranty (in months)	36
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	932 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	51 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2 kg CO2 eq.
Carbon footprint of the installation phase [A5]	1 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	876 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

4-in-1 outlet for increased flexibility



Acts as any of these outlet types:



C13



C15



C19



C21

Multiple color options available











